Product data sheet
Characteristics

PDIY7
APC Workshop SurgeArrest 7 Outlets

Commercial status
This Product is Obsolete : FEB 14, 2024

⚠ This Product is Obsolete

Overview

Lead time	Usually Ships within 8 Weeks

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	8 Ft (2.44 m)
Number of cables	1
Provided equipment	User Manual

Physical

Color	Yellow
Height	14.96 In (38 cm)
Width	2.76 In (7 cm)
Depth	1.77 In (4.5 cm)
Net Weight	1.59 Lb(US) (0.72 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz auto-sensing

Output

Number of power socket outlets	7
Outlet standard	NEMA 5-15R

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Conformance

UL 1449 TVSS Rating	330
Product Certifications	CSA
Standards	UL 1449
Equipment protection policy	Lifetime : $5000

Environmental

Ambient Air Temperature for Operation	32…104 °F (0…40 °C)
Relative Humidity	0…95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5…113 °F (-15…45 °C)
Storage Relative Humidity	0…95 %
Storage altitude	0…50000 Ft (0.00…15240.00 m)

Surge Protection and Filtering

EP Joule Rating	820 J
NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	20 DB
Peak current	12 KAcommon mode 6 KAnormal mode
Surge energy rating	800 J

Ordering and shipping details

GTIN	731304238324
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.96 In (38 cm)
Package 1 Width	2.01 In (5.1 cm)
Package 1 Length	4.29 In (10.9 cm)
Package 1 Weight	1.10 Lb(US) (0.5 kg)
SCC14	10731304238321

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Limited Lifetime

Product Life Status :	End of commerc. announced