Product data sheet
Characteristics

2510KSJ4B
Manual Switch - Jumbo SS Flush - 3P - Key Operated - Red Indicator - 600VAC

⚠ This Product is Obsolete

Commercial status
This Product is Obsolete : NOV 11, 2020

Main

Product or Component Type	Single Unit Manual Switch
Range of Product	K

Complementary

Line Rated Current	30 A
Maximum Horse Power Rating	2 Hp 115 V AC 1 Hp 90 V DC 2 Hp 115 V DC 1.5 Hp 230 V DC 7.5 Hp 230 V AC 10 Hp 460 V AC 10 Hp 575 V AC
[Ue] rated operational voltage	600 V AC 230 V DC
Poles description	3P
Control Type	Key
Phase	3 phase
Local signalling	Red indicator, 208...277 V
Motor starter type	Non reversing
Electrical Connection	Screw clamp terminals
AWG gauge	AWG 14...AWG 10 copper
Height	5.25 In (133.35 mm)
Width	3.5 In (88.90 mm)
Depth	2.5 In (63.50 mm)

Environment

Product Certifications	UL listed file E42243 CCN NLRV[RETURN]CSA LR25490 class 3211 05
NEMA degree of protection	Not rated (flush plate) Stainless Steel oversized

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	21102-2510,2511,2512 K
Discount Schedule	CP1
GTIN	00785901121541
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh free of SVHC	Yes
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months

Product Life Status : End of commerc. - Block