Product data sheet
Characteristics

2510MBW11V03P11
Manual Starter - NEMA 4 Stainless Steel - 2P - Size M0 - Red Indicator - 600VAC

⚠ This Product is Obsolete

Commercial status
This Product is Obsolete : JUN 30, 2020

Main

Product or Component Type	Manual Starter
Range of Product	M
NEMA size	M-0

Complementary

Control Type	Push-button
Local signalling	Red indicator, 240 V
Maximum Horse Power Rating	1 Hp 115 V AC, 1 phase 2 Hp 230 V AC, 1 phase
[Ue] rated operational voltage	600 V AC
Poles description	2P
Motor starter type	Non reversing
Electrical Connection	Pressure wire clamp
Thermal overload type	Melting alloy
Number of thermal units required	1
AWG gauge	AWG 14...AWG 8 copper
Auxiliary contact composition	Without
Height	10.92 In (277.37 mm)
Width	5.78 In (146.81 mm)
Depth	5.76 In (146.30 mm)

Environment

Product Certifications	UL listed file E42243 CCN NLRV[RETURN]CSA LR60905 class 3211 05
NEMA degree of protection	NEMA 4/4X brushed stainless steel

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	21103-2510,2511,2512 M,T
Discount Schedule	CP1
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
PVC free	Yes

Contractual warranty

Warranty	18 months

Product Life Status : End of commerc. - Block