Product data sheet
Characteristics

8903LO1200V02Y145

8903L electrically held lighting contactor, 12 P, 12 NO, 30 A, 600 V, 110/120 V 50/60 Hz coil, open

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Product or Component Type	Electrically Held Lighting Contactor
Range of Product	8903L
Control circuit	Separate control circuit

Complementary

[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Inrush power in VA	180 VA 60 Hz 170 VA 50 Hz
Hold-in power consumption in VA	35 VA 60 Hz 35 VA 50 Hz
Line Rated Current	20 A tungsten 30 A fluorescent
Poles description	12P 12 NO
Control type	No control units
Local signalling	No indicator
Additional included device	Transient voltage suppression
Electrical Connection	Screw-clamp terminals
Height	5.00 In (127 mm)
Depth	3.11 In (79 mm)
Width	5.63 In (143 mm)

Environment

NEMA degree of protection	Not rated (open device)
Product Certifications	UL Listed[RETURN]CSA

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.50 In (19.05 cm)
Package 1 Width	13.50 In (34.29 cm)
Package 1 Length	8.00 In (20.32 cm)
Package 1 Weight	4.38 Lb(US) (1.987 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months

Product Life Status : End of commerc. announced