Product data sheet
Characteristics

9001KP35L31
Pilot light, Harmony 9001K, metal, polycarbonate, fresnel, blue, 30mm, 24-28V

Main

Range of product	Harmony 9001K
Product or component type	Pilot light
Device short name	K

Complementary

Bezel material	Metal
Mounting diameter	30 Mm
Lens type	Fresnel plastic
Cap/operator or lens colour	Blue
Light source	Incandescent
Bulb base	BA 9s
Light block supply	Full voltage 28 V Direct 24 V
Connections - terminals	Screw clamp terminals, 1 x 0.22...2 x 1.5 mm² conforming to IEC 60947-1
Shape of screw head	Round
Operating position	Any position
Light source	Incandescent bulb
[Us] rated supply voltage	24...28 V AC/DC
Operating mode	Normal
Device presentation	Complete product
Lens type	Fresnel
[Us] rated supply voltage	24...28 V
Light block supply	Full voltage
Lens material	Polycarbonate
Size	30 mm

Environment

Product certifications	UL listed file E42259 CCN NKCR[RETURN]CE[RETURN]CSA L-R25490 class 3211 03
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.903 Cm
Package 1 Width	5.08 Cm
Package 1 Length	32.774 Cm
Package 1 Weight	226.796 G

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Product Life Status : Commercialised