Product data sheet
Characteristics

9080GP638
Terminal Block Assembly, Pressure Wire Clamp, Natural Color, 600VAC/DC 40AMP

Commercial status
This Product is Obsolete :

⚠ This Product is Obsolete

Main

Range of Product	9080G
Product or Component Type	Terminal block
Color	Natural

Complementary

[Ue] rated operational voltage	600 V AC/DC
Line Rated Current	40 A UL 40 A CSA
Kit composition	1 end barrier 2 end clamp(s) 1 mounting track 38 terminal blocks
AWG gauge	AWG 18...AWG 12 copper
Mounting Support	9080GH track
Product Certifications	UL recognized E60616 CCN XCFR2[RETURN]CSA file 62144 class 6228 01[RE-TURN]CE
Ambient Air Temperature for Operation	-40…257 °F (-40…125 °C)
Connections - terminals	Clamp terminal zinc plated- steel 18…20 lbf.in (2.03…2.26 N.m) : AWG 18...AWG 10 copper)
Height	1.48 In (37.59 mm)
Width	1.8 In (45.72 mm)
Depth	16 In (406.40 mm)

Ordering and shipping details

Category	21702-9080 G (NOT GCB)
Discount Schedule	CP5
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	16.00 Oz (453.592 g)

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty	18 months

Product Life Status :	End of commerc. - Block