Product data sheet
Characteristics

CSU76663330
Stago - internal riser formed - 60x330 mm - stainless steel AISI 304

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.



⚠ End of Commercialisation

Commercial status
End of Commercialisation : JAN 03, 2022

Main

Range of product	Stago
Range	Stago
Product or component type	Riser
Device application	Cable management

Complementary

Operating angle	90 °
Direction change type	Vertical
Inner radius	180 Mm
Adjustment	Fixed
Shape	Bended
Product destination	Cable tray ES114 H= 60 mm W= 330 mm
Fixing mode	By screw
Material	Stainless steel AISI 304
Atmospheric-corrosivity category	C5-I
Thickness	1 Mm
Height	236 Mm
Width	333 Mm
Depth	236 Mm
Net weight	2.15 Kg / set of 1

Environment

Environmental characteristic	Area with almost permanent high levels of humidity and airborne pollution tunnels and dockyards

Product Life Status : End of commerc. - Block

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.