Product data sheet
Characteristics

E84426-15_SZ
15A 1 Gang 3 Round Pin Socket with Shutter, Silver Bronze

Main

Product or component type	Power socket-outlet
Outlet poles configuration	2P + E
Load type	No inductive load
Cover frame colour tint	Silver bronze
Cover plate colour tint	Bronze

Complementary

Device mounting	Surface Flush
Rated current	15 A at 250 V AC 50 Hz
Number of gangs	1 gang
Material	Brass contact Polycarbonate base Polycarbonate grid plate Polycarbonate surround Phosphor bronze contact
Connections - terminals	Folded terminal
Width	87 Mm
Height	87 Mm
Depth	8 Mm

Environment

Ambient air temperature for operation	-5…40 °C
Relative humidity	0…95 %
Environmental characteristic	UV resistant indoor use
Operating altitude	2000 m
Standards	BS 546
Standards	BS 546

Contractual warranty

Warranty	18 months

Product Life Status : Commercialised

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.