Product data sheet
Characteristics

GU1514WBC
Plate switch, Ultimate Low profile, 2-way, screw terminals, IP20, chrome

Main

Range of product	Ultimate
Range	Ultimate
Aesthetic name	Low profile
Product or component type	Plate switch
Control type	Rocker
Switch function	2-way
Rated current	16 AX at 230 V AC

Complementary

Connections - terminals	Screw terminals
Material	Steel
Quantity per set	Set of 1
Number of gangs	1 gang
Device mounting	Wall mounted
Height	88 Mm
Width	88 Mm
Depth	24 Mm

Environment

Standards	BS EN 60669-1
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 Cm
Package 1 Width	9.5 Cm
Package 1 Length	9.6 Cm
Package 1 Weight	165.8 G
Unit Type of Package 2	CAR
Number of Units in Package 2	100
Package 2 Height	22 Cm
Package 2 Width	42.5 Cm
Package 2 Length	50 Cm
Package 2 Weight	17.168 Kg
Unit Type of Package 3	PAM

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Number of Units in Package 3	1600
Package 3 Height	104.5 Cm
Package 3 Width	100 Cm
Package 3 Length	120 Cm
Package 3 Weight	294.688 Kg

Offer Sustainability

REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months

Product Life Status : Commercialised