Product data sheet
Characteristics

ISM20123
OptiLine 45 - pole - tension-mounted - two-sided - white - 3900-4300 mm

Commercial status
End of Commercialisation : MAY 30, 2017

⚠ End of Commercialisation

Main

Range	OptiLine
Product name	OptiLine 45
Cabling installation system	Pole
Product or component type	Pole
Device presentation	Empty
Type of pole	Two-sided
Pole/post surface finish	Powder coated
Pole fixing mode	Tension-mounted
Socket additional information	Unearthed

Complementary

CMS inst product add info	Adjustability of ceiling fixing 400 mm
Colour tint	White
Front opening size	45 mm
Material	Aluminium powder coated
Quantity per set	Set of 1
Height	3900…4300 Mm
Width	116 Mm

Environment

Ambient air temperature for operation	-25…60 °C
IP degree of protection	IP40

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	390 Cm
Package 1 Width	11.6 Cm
Package 1 Length	9 Cm
Package 1 Weight	15.62 Kg

Product Life Status : End of commerc. - Block

ISM20123 may be replaced by any of the following products:

ISM20123P

OptiLine 45 - pole - tension-mounted - two-sided - polar white - 3900-4300 mm

Qty 1

Substitution date: |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.