Product data sheet
Characteristics

MIP11106S
mini Pragma surface enclosure - 1 x 6 modules - smoked door

Commercial status
End of Commercialisation : MAR 23, 2020

⚠ End of Commercialisation

Main

Range	Mini Pragma
Product or component type	Enclosure
Enclosure type	Modular enclosure
Number of 18 mm modules per row	6
Number of horizontal rows	1
Type of front cover	Smoked
Width	160 Mm outside:
Height	198 Mm outside:
Depth	95.5 Mm outside:

Complementary

Enclosure mounting	Surface
9 mm pitches	12
Total number of 18 mm modules	6
[In] rated current	63 A
Type of rail	35 mm asymmetrical rail
Cable entry	1 bare flange 1 trunking flange
Terminal block function	Earth
Number of terminal blocks	1 earth (screwed) with 4 outgoers
Distribution block outgoers	1 x 16 mm² for earth 1 x 6 mm² for earth 2 x 10 mm² for earth
Enclosure material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Door: smoked Front face: white (RAL 9003)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality labels	IMQ
Fire resistance	Back part: 750 °C Door: 650 °C Front face: 750 °C
IP degree of protection	IP40
IK degree of protection	IK07
Ambient air temperature for operation	-25…60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.7 Cm
Package 1 Width	16 Cm
Package 1 Length	19.5 Cm
Package 1 Weight	0.47 Kg

Contractual warranty

Warranty	18 months

Product Life Status : End of commerc. - Block