APC Back-UPS[™]400

Part Number: BE400-GR

Battery Backup with Surge Protection for Computers and Electronics

APC by Schneider Electric's Back-UPS 400 provides enough battery backup power so you can work through short length power outages. It also safeguards your equipment against damaging surges and spikes that travel along utility and phone lines. The Back-UPS series is "greener" than ever, using an ultra-efficient design that consumes less power during normal operation than any other battery backup in its class. This reduces your energy costs and environmental impact. Combined with all of the standard features of the Back-UPS series, the 400 is the perfect unit to protect your productivity from the constant threat of bad power and lost data.

Product Applications:

PC
Home networking (DSL-modem or wireless router)
CCTV
Networking storage (NAS)
POS Equipment
Landline cordless phone





Product Features:

- LED Indicator and Audible Alarms
 Quickly understand the unit and power status
 through visual and audible indicators.
- 8 battery backup and surge protected sockets
 4 battery backup and surge protection
 Keep critical electronic equipment running when the power goes out or fluctuates at dangerous levels, so you can protect your work and save your data.
 - 4 surge protection only

Protect your secondary electronics from harmful surges and spikes without reducing battery capacity used to run primary electronics during power outages.

- Data Line Surge Protection
 Provides protection of connected equipment from damaging power surges on telephone and Ethernet data lines.
- Push Button Circuit Breaker
 Provides for easy recovery from circuit overloads
 and protects your fuse box and electronics from
 electrical damage.
- Automatic Diagnostic Testing
 Periodic battery self-test ensures early detection of a battery that needs to be replaced.
- 2 or 3 Yr Warranty*

 APC offers a 2 or 3 year warranty with free technical phone and online support, providing customer peace of mind.
 - *Warranty differs by region



Back-UPS 400 Specifications	
Model Number	BE400-GR
Output	
Output Capacity	400VA / 240 Watts
Output Voltage / Frequency (On utility)	230V / 47 - 63 Hz
Output Voltage / Frequency (On battery)	230V +/-8%, 50 Hz +/- 0.1% for 50 Hz nominal
Output Connections	8 Schuko CEE 7 sockets (4 battery backup and surge protection, 4 surge protection only)
Waveform Type	Stepped Approximation to Sine Wave
	Input
Input Voltage / Frequency	230V, 50/60 Hz
Input Connection	1.8M power cord Schuko CEE 7
S	Surge Protection
AC Power Surge Protection	All sockets
Data Line Surge Protection	Analog phone line for phone/fax/modem/DSL (RJ-11 connector), Network line - 10/100 Base-T Ethernet (RJ-45 connector)
	Physical
Unit Dimensions (H x W x D)	86 x 230 x 285 mm
Unit Weight	5.4 Kg
Shipping Dimensions (W x D x H)	360 x 125 x 285 mm
Shipping Weight	5.6 Kg
Color	Black
UPC Code	731304233367
	Battery
Battery Type	Maintenance-free, sealed lead-acid battery with suspended electrolyte: leak proof
Battery Size	12 volt, 6 Ah
Management	
Alarms	Visual (LED) and audible alarms
Warranty	2 or 3 Years Repair or Replace (dependent on region)
Equipment Protection Policy	Lifetime: 100,000 Euro (not available in all regions)

APC by Schneider Electric

132 Fairgrounds Rd West Kingston, RI 02892

