







This drawing is the property of Schneider Electric Automation GmbH. It is furnished to you for confidential information purposes only and is not to be disclosed to anyone else or reproduced or used for manufacturing purposes without the express permission of Schneider Electric Automation GmbH. Offenders will be held liable for the payment of damages.

©Schneider Electric Automation GmbH. Schutzvermerk nach DIN ISO 16016 beachten / copyright reserved. Diese Zeichnung ist Eigentum der Schneider Electric Automation GmbH. Sie wird Ihnen nur zu vertraulichen Informationszwecken überlassen. Ohne die ausdrückliche Genehmigung der Schneider Electric Automation GmbH ist die Vervielfältigung oder Verwertung sowie die Weitergabe dieser Zeichnung an Dritte verboten. Zuwiderhandlungen verpflichten zum Schadensersatz.







<b>Allgemeintoleranzen nach</b> / <i>general tolerances according to</i> DIN ISO 2768 mK <b>Oberflächenangaben nach</b> / <i>indicating surface finish according to</i> DIN ISO 1302 <b>Tolerierung nach</b> / <i>toleration according to</i> ISO 8015		<b>Werkstoff</b> / <i>material</i> <b>Stahl</b>		<b>Teil ist RoHS-konform</b> / <i>part is RoHS-compliant</i>		<b>RoHS</b> COMPLIANT 2002/95/EC	
		<b>Halbzeug</b> / <i>pre-product</i> -					
		<b>Oberfläche</b> / <i>surface finish</i> -					
		<b>Masse</b> / <i>weight</i> -		<b>Bezeichnung</b> / <i>part name</i>			
<b>Massstab</b> / <i>scale</i> 1:1				<b>Daisy Chain Connector</b>  ILM62DCA000			
		<b>Volumen</b> / <i>volume</i> 0,00mm <sup>3</sup>					
		<b>alle Maße in mm</b> / <i>all dimensions in mm</i>					
		<b>Zeichnungsnummer</b> / <i>drawing no.</i> SE031032		<b>Index</b> S00		<b>Artikelnummer</b> / <i>part number</i>	<b>Blatt</b> / <i>sheet</i> 1 of 2
				<b>EDV Nr.</b> / <i>file name</i> SE031032.idw			

This drawing is the property of Schneider Electric Automation GmbH. It is furnished to you for confidential information purposes only and is not to be disclosed to anyone else or reproduced or used for manufacturing purposes without the express permission of Schneider Electric Automation GmbH. Offenders will be held liable for the payment of damages.

©Schneider Electric Automation GmbH. Schutzvermerk nach DIN ISO 16016 beachten / copyright reserved. Diese Zeichnung ist Eigentum der Schneider Electric Automation GmbH. Sie wird Ihnen nur zu vertraulichen Informationszwecken überlassen. Ohne die ausdrückliche Genehmigung der Schneider Electric Automation GmbH ist die Vervielfältigung oder Verwertung sowie die Weitergabe dieser Zeichnung an Dritte verboten. Zuwiderhandlungen verpflichten zum Schadensersatz.

A  
B  
C  
D  
E  
F



<div>Allgemeintoleranzen nach / general tolerances according to DIN ISO 2768 mK</div> <div>Oberflächenangaben nach / indicating surface finish according to DIN ISO 1302</div> <div>Tolerierung nach / toleration according to ISO 8015</div>		Werkstoff / material		Stahl		Teil ist RoHS-konform / part is RoHS-compliant		RoHS COMPLIANT 2002/95/EC		
		Halbzeug / pre-product		-						
		Oberfläche / surface finish		-						
		Masse / weight		-		Bezeichnung / part name		Daisy Chain Connector  ILM62DCA000		
Massstab / scale		1:1		Volumen / volume		0,00mm <sup>3</sup>				
<div>Schneider Electric</div>		alle Maße in mm / all dimensions in mm				Artikelnummer / part number				
		Zeichnungsnummer / drawing no.		Index						
		SE031032		S00		Blatt / sheet 2 of 2  Format / size A3				
		EDV Nr. / file name SE031032.idw								

