Product data sheet
Characteristics

PH8U2W
APC Home Office SurgeArrest 8 Outlets with 2 USB Charging Ports (5V, 2.4A in total), 120V White

Commercial status
End of Commercialisation : APR 24, 2024

⚠ End of Commercialisation

Overview

Lead time	Usually in Stock

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	1.83 M
Number of cables	1
Provided equipment	User manual

Physical

Colour	White
Height	3 Cm
Width	7.7 Cm
Depth	29.7 Cm
Net weight	0.67 Kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Maximum line current	15 A
Network frequency	50/60 Hz
Maximum input current	15 A
Switching current capacity	15 A

Output

Number of power socket outlets	8
Outlet standard	NEMA 5-15R

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Conformance

Product certifications	MET Canada[RETURN]MET USA
Standards	FCC part 15 class B UL 1363 UL 1449 UL 60950-1
Equipment protection policy	Lifetime : $150000

Environmental

Ambient air temperature for operation	0…40 °C
Relative humidity	0…95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15…45 °C
Storage Relative Humidity	0…95 % non-condensing
Storage altitude	0.00…15240.00 M

Surge Protection and Filtering

Response time	1 ns common mode
Common mode rejection	40 DB
Peak current	56 KAcommon mode 28 KAnormal mode
Surge energy rate	2160 J

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.8 Cm
Package 1 Width	33.5 Cm
Package 1 Length	14.5 Cm
Package 1 Weight	0.78 Kg
SCC14	10731304336201

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Limited Lifetime

Product Life Status : Post commercialisation