Product data sheet
Characteristics

QON24L70
Load center interior, QO, mounting base, 1 phase, 2 spaces, 70A main lugs, OEM

Green Premium

Product availability: Stock - Normally stocked in distribution facility

Price*: 50.00 USD



Main

Product or Component Type	Mounting base
Range of Product	QO
Load center type	Main lugs
Line Rated Current	70 A
Number of spaces	2
Short-circuit current	10 KA
Phase	1 phase
[Ue] rated operational voltage	120/240 V AC

Complementary

AWG gauge	AWG 14...AWG 4 copper AWG 12...AWG 3 aluminium
Wiring configuration	3-wire
Product Certifications	UL[RETURN]CSA
Height	1.34 In (34 mm)
Width	4.21 In (107 mm)
Depth	1.89 In (48 mm)
Net Weight	3.09 Lb(US) (1.400 kg)

Ordering and shipping details

Category	US1DE3A00909
Discount Schedule	DE3A
GTIN	785901804598
Returnability	Yes
Country of origin	MX

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.90 In (4.826 cm)
Package 1 Width	2.80 In (7.112 cm)
Package 1 Length	4.20 In (10.668 cm)
Package 1 Weight	5.20 Oz (147.463 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months

Product Life Status : Commercialised