Product data sheet
Characteristics

SDN3100360
Sedna - single socket outlet, side earth - 16A IP44 shutter, lid, wo frame alum



Commercial status
End of Commercialisation : DEC 30, 2023

⚠ End of Commercialisation

Main

Range of product	Sedna
Product or component type	Socket-outlet
Device presentation	Without frame
Outlet poles configuration	2P + E with shutters
Outlet standard description	Side earth
Rated current	16 A at 250 V AC
Market segment	Small commercial Residential
Socket additional information	Lid

Complementary

Wire stripping length	13 Mm
Width	71 Mm
Depth	49.3 Mm
Net weight	0.077032 Kg
Projecting depth	18 Mm
Fixing mode	Claws, span of claws working range: 52…69 mm Screws
Height	71 Mm
Surface finish	Glossy
Material	PC
Cable stiffness	Rigid Flexible
Number of cables	2 cable(s) 2.5 mm²
Connections - terminals	Lift terminals
Power range	3680 W

Environment

IP degree of protection	IP44
Product certifications	GOST-R
Standards	IEC 60884-1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 Cm
Package 1 Width	7.000 Cm
Package 1 Length	7.000 Cm
Package 1 Weight	79.500 G
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.500 Cm
Package 2 Width	18.500 Cm
Package 2 Length	27.500 Cm
Package 2 Weight	876.000 G
Unit Type of Package 3	S04
Number of Units in Package 3	120
Package 3 Height	30.000 Cm
Package 3 Width	40.000 Cm
Package 3 Length	60.000 Cm
Package 3 Weight	11.044 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months

Product Life Status : End of commercialisation