


| ITEM | TORQUE |
|---|---|
| 9 | 20-30 IN/LBS |
| 24 | 20-30 IN/LBS |
| 25 | 8-10 IN/LBS |
| 32 | 20-30 IN/LBS |

NOTE:

1. PLACE MOISTURE LABEL, ITEM #14, ON INSIDE OF POST ABOVE DRAIN HOLE, ARROWS ON LABEL TO POINT DOWN AT BRACKETS.
2. INSURE THAT ALL TERMINAL SCREWS ON THE DUPLEX RECEPTACLE ARE TIGHTENED DOWN.
3. ASSEMBLE THE GREEN WIRE FROM THE DUPLEX RECEPTACLE INTO ITEM #23 - TIGHTEN TO 20 IN-LBS.
4. PLACE CIRCUIT ID NUMBERS, ITEM #18, ON TRIM ADJACENT TO BREAKERS & RECEPTACLES AS SHOWN ABOVE.
5. ATTACH DIRECTORY LABEL, ITEM #15, ON TRIM, ITEM #8.
6. ATTACH WARNING LABEL, ITEM #22, TO UNDERSIDE OF COVER, SO THAT IT MAY BE READ WHEN COVER IS OPEN.
7. AFFIX WIRING DIAGRAM, ITEM #10 TO UNDERSIDE OF COVER, SO THAT IT MAY BE READ WHEN COVER IS OPEN.
8. SECURE ENVELOPE ASSEMBLY, ITEM #19, TO DEVICE WITH TAPE, ITEM #20.
9. ASSEMBLE THE GREEN GROUND WIRE FROM THE 30A. RECEPTACLE INTO THE NEUTRAL BAR ASSEMBLY, ITEM 23, AND TORQUE THE WIRE BINDING SCREW TO 15-25 LB-IN
10. PLACE INSTRUCTION LABEL, ITEM #34, INSIDE DEVICE BEFORE FASTENING INTERIOR TRIM, ITEM #8.
11. ADD THE BREAKER INSTRUCTIONS SHEET INSIDE THE DEVICE.
12. SEE DETAIL A FOR WIRING INFORMATION.
13. (A) PLACE INSTRUCTIONS CARD #40 BETWEEN COVER AND TRIM.
14. (B) ATTACH LABEL THAT COMES WITH GFI BREAKER AS SHOWN.

| REV | ECO/ECN | DATE | BY | REVISION DESCRIPTION |
|---|---|---|---|---|
| B | RS07116 | 22FEB2007 | AAR | ADD ITEM 50, NOTE 14 AND SHOW LOCATION OF GFI BREAKER'S LABEL. |
| A | RS06174 | 03/10/05 | AAR | ADD NOTE 13, ITEM #40 |

THIRD ANGLE

PROPRIETARY PROPERTY OF SQUARE D COMPANY. NOT TO BE REPRODUCED BY ANY MEANS OR USED TO FURNISH INFORMATION TO OTHERS WITHOUT THE EXPLICIT CONSENT OF SQUARE D COMPANY. ALL RIGHTS RESERVED. © 2001, SQUARE D COMPANY

DIMENSIONS ARE IN INCHES

| STANDARD TOLERANCES UNLESS OTHERWISE SPECIFIED: | | | | |
|---|---|---|---|---|
| LINEAR | THREE PLACE DECIMAL ± .005 (.13MM) | TWO PLACE DECIMAL ± .02 (.5MM) | | |
| ANGLES | DIMENSIONED ± 1° | UNDIMENSIONED 90° ± 2° | | |
| HOLE DIAMETER | THREE PLACE DECIMAL +.002 (.05MM) | TWO PLACE DECIMAL ± .015 (.38MM) | FRACTIONAL NUMBER OR LETTER SIZE +.004 (.1MM) -.002 (.05MM) | |

TITLE: CATALOG ASSEMBLY

QO4RVP100DG E04

CLASS TYPE FORM SERIES

| SCALE | DRAWN | CHKD. | DATE | ECO/ECN |
|---|---|---|---|---|
| FULL | AAR | SLC | 02/08/06 | PE05178 |

PRINTS TO

SQUARE D

SIZE C NUMBER 40103-047-50 SHEET 1 OF 1