



Commercial status

This Product is Obsolete : NOV 10, 2023

⚠ This Product is Obsolete

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Color	Black
PDU Type	Switched
Cable length	12 Ft (3.7 m)
Number of cables	1
Provided Equipment	Cord retention bracket(s) Horizontal mounting brackets User Manual Installation guide

Complementary

Main Input Voltage	100 V 120 V
Height	1.7 In (4.4 cm)
Width	17.5 In (44.5 cm)
Output voltage	120 V
Depth	4.3 In (10.8 cm)
Net Weight	5.004 Lb(US) (2.27 kg)
Mounting location	Front
Mounting preference	No preference
Input Connection Type	NEMA 5-15P
Mounting Mode	Rack-mounted
Number of rack unit	1U
Mounting position	Horizontal
Line Rated Current	12 A
Acceptable Input Voltage	100...120 V
Input current limits	15 A
Load Capacity	1440 VA

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Input Frequency	50/60 Hz
Number of power socket outlets	8 NEMA 5-15R

Environment

Product Certifications	cUL Listed[RETURN]UL Listed
Standards	FCC Part 15 class A ICES-003
Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 Ft (0.0000000000...15240.0000000000 m)




Ordering and shipping details

GTIN	731304205722
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 In (7 cm)
Package 1 Width	13.5 In (34.3 cm)
Package 1 Length	18.5 In (47 cm)
Package 1 Weight	7.61 Lb(US) (3.45 kg)

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **End of commercialisation**

AP7900 may be replaced by any of the following products:



AP7900B

Rack PDU, Switched, 1U, 15A, 100/120V, (8)5-15

Qty 1

Substitution date: |