



EAN Code: 0731304293361



### Main

Product or component type	Replacement battery cartridge
Battery type	Lead-acid battery
Provided equipment	Installation guide

### Batteries & Runtime

Battery location	Internal battery
Number of battery blocks per string	2
Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Stand alone battery stack
Battery voltage	24 V
Number of battery replacement quantity	1

### Physical

Height	107 Mm
Width	107 Mm
Depth	144 Mm
Product weight	3.3 Kg
Mounting mode	Not rack-mountable

### Output

Battery capacity	4.5 Ah
------------------	--------

### Environmental

Ambient air temperature for operation	0...50 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...45 °C
Storage altitude	0...15240 M
Storage Relative Humidity	0...95 %

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	22.9 Cm
Package 1 Width	22.9 Cm
Package 1 Length	22.9 Cm
Package 1 Weight	3.75 Kg

## Offer Sustainability

Recyclability potential, in %	1
Total lifecycle Carbon footprint	24 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	12.347787248964313
Carbon footprint of the manufacturing phase [A1 to A3]	12 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.5263690955896204
Carbon footprint of the distribution phase [A4]	0.5 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.29130389470715895
Carbon footprint of the installation phase [A5]	0.3 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1.0124525275438332
Carbon footprint of the use phase [B2, B3, B4, B6]	1 kg CO2 eq.
Sustainable packaging	No
Carbon footprint of the end-of-life phase [C1 to C4]	9.518198782388419
Carbon footprint of the end-of-life phase [C1 to C4]	10 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Total lifecycle Carbon footprint	24
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	25764278-9ac2-4c03-941a-d133167ad10f
REACH Regulation	Reference contains Substances of Very High Concern above the threshold <a href="#">↗</a>
EU RoHS Directive	Compliant <a href="#">↗</a>
End of life manual availability	<a href="#">End Of Life Information</a>
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and

## Logistical informations

Country of origin	US
-------------------	----

## Contractual warranty

Warranty (in months)	24
----------------------	----

Product Life Status : **Commercialised**