

# Product data sheet

## Characteristics

# APCRBC106

APC Replacement Battery Cartridge 106 with 2 Year Warranty



EAN Code: 0731304244400



### Main

Product or component type	Replacement battery cartridge
Battery type	Lead-acid battery
Provided equipment	All required connectors Installation guide

### Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0
Battery voltage	12 V
Number of battery replacement quantity	1

### Physical

Colour	Black
Height	48 Mm
Width	102 Mm
Depth	140 Mm
Product weight	2.5 Kg
Mounting mode	Not rack-mountable
USB compatible	No

### Output

Battery capacity	6 Ah
------------------	------

### Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	0...40 °C
Storage altitude	0...3048 M
Storage Relative Humidity	0...95 %

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.9 Cm
Package 1 Width	17.5 Cm
Package 1 Length	21.3 Cm
Package 1 Weight	2.77 Kg
SCC14	10731304244407

## Offer Sustainability

Recyclability potential, in %	1
Total lifecycle Carbon footprint	18 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	9.354384279518419
Carbon footprint of the manufacturing phase [A1 to A3]	9 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.398764466355773
Carbon footprint of the distribution phase [A4]	0.4 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.22068476871754467
Carbon footprint of the installation phase [A5]	0.2 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0.6749683516958889
Carbon footprint of the use phase [B2, B3, B4, B6]	0.7 kg CO2 eq.
Sustainable packaging	No
Carbon footprint of the end-of-life phase [C1 to C4]	7.21075665332456
Carbon footprint of the end-of-life phase [C1 to C4]	7 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Total lifecycle Carbon footprint	18
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
REACH Regulation	Reference contains Substances of Very High Concern above the threshold <a href="#">↗</a>
EU RoHS Directive	Compliant <a href="#">↗</a>
End of life manual availability	<a href="#">End Of Life Information</a>
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and

## Logistical informations

Country of origin	PH
-------------------	----

## Contractual warranty

Warranty (in months)	24
----------------------	----

Product Life Status : **Commercialised**