



中国国家强制性产品认证证书

证书编号：2026010304857505

认证委托人名称及地址

施耐德电气（中国）有限公司上海分公司
上海市普陀区绥德路 669 号

生产者名称及地址

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

生产企业名称及地址

无锡普洛菲斯电子有限公司
江苏省无锡市汉江路 20 号

产品名称和系列、型号、规格

软起动器

ATS430C14S6, ATS430C17S6 ; 详见附页

产品标准和技术要求

GB/T 14048.6-2016

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》
(CNCA-C03-02:2024) 的要求，特发此证。

发证日期：2026 年 04 月 01 日 有效期至：2031 年 03 月 31 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站 (www.cnca.gov.cn) 查询。



签发：

刘江



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





中国国家强制性产品认证证书

证书编号: 2026010304857505

证书附页: 第 1 页 共 1 页

ATS430C14S6, ATS430C17S6 Uimp: 6kV; Ui: 600V; Ith: ATS430C14S6: 140A, ATS430C17S6: 170A; Ue: 208V~600V; Ie: ATS430C14S6: 140A, ATS430C17S6: 170A; Pe: 详见下表; 使用类别: AC-53a; 极数: 3P

	HP @208V	HP @230V	HP @460V	HP @575V	kW @230V	kW @400V	kW @440V	kW @500V
ATS430C14S6	40	50	100	125	37	75	75	90
ATS430C17S6	50	60	125	150	45	90	90	110

3.3 型号的解释(Explanation of model/ type):

	<u>ATS430</u>	<u>C14</u>	<u>S6</u>
	1	2	3
1 产品系列	ALTISTART 430		
2 产品规格	C14: 140A	C17: 170A	
3 电压等级	S6 额定电压(208V 至 600V)		

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2026010304857505

NAME AND ADDRESS OF THE APPLICANT

Schneider Electric (China) Co. Ltd. Shanghai Branch
No. 669, Suide Road, Putuo District, Shanghai, P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

NAME AND LOCATION OF THE FACTORY

Wuxi Pro-face Co., Ltd
No.20,Hanjiang Road, Wuxi,Jiangsu, Wuxi, China

PRODUCT NAME,MODEL AND SPECIFICATION

Soft Starter
ATS430C14S6 , ATS430C17S6 ;

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.6-2016

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Apr.01,2026

Valid until: Mar.31,2031

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2026010304857505

Appendix: Page 1 of 1

ATS430C14S6, ATS430C17S6 Uimp: 6kV; Ui: 600V; Ith: ATS430C14S6: 140A, ATS430C17S6: 170A; Ue: 208V~600V; Ie: ATS430C14S6: 140A, ATS430C17S6: 170A; Pe:see the blow;Utilization Category: AC-53a;pole: 3P

	HP @208V	HP @230V	HP @460V	HP @575V	kW @230V	kW @400V	kW @440V	kW @500V
ATS430C14S6	40	50	100	125	37	75	75	90
ATS430C17S6	50	60	125	150	45	90	90	110

3.3 型号的解释(Explanation of model/ type):

	<u>ATS430</u>	<u>C14</u>	<u>S6</u>
	1	2	3
1 产品系列	ALTISTART 430		
2 产品规格	C14: 140A	C17: 170A	
3 电压等级	S6 额定电压(208V 至 600V)		

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



中国国家强制性产品认证证书

证书编号：2024010304660704

认证委托人名称及地址

施耐德电气（中国）有限公司上海分公司
上海市普陀区绥德路 669 号

生产者名称及地址

Schneider Electric Industries SAS
35 Rue Joseph Monier, 92500 Rueil-Malmaison France

生产企业名称及地址

PT. Schneider Electric Manufacturing Batam
Jl Beringin Lot 4, Lot 208, Lot 1, Lot 15, Lot 16, DAN Lot 16A BIP Muka Kuning
Kel. Muka Kuning Kec. Sungai Beduk - Batam, Indonesia

产品名称和系列、型号、规格

软起动机

ATS430C14S6, ATS430C17S6; Uimp:6kV;Ui:600V;Ith: ATS430C14S6:140A,
ATS430C17S6:170A;Ue: 208V~600V; Ie: ATS430C14S6:140A, ATS430C17S6:170A;Pe:
ATS430C14S6: 37kW(230V), 75kW(400V), 75kW(440V), 90kW(500V); ATS430C17S6:
45kW(230V), 90kW(400V), 90kW(440V), 110kW(500V);使用类别: AC-53a;极数: 3P

产品标准和技术要求

GB/T 14048. 6-2016

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》
(CNCA-C03-02:2024) 的要求，特发此证。

发证日期：2024 年 07 月 19 日 有效期至：2029 年 07 月 18 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。



签发：

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010304660704

NAME AND ADDRESS OF THE APPLICANT

Schneider Electric (China) Co. Ltd. Shanghai Branch
No. 669, Suide Road, Putuo District, Shanghai, P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

Schneider Electric Industries SAS
35 Rue Joseph Monier, 92500 Rueil-Malmaison France

NAME AND LOCATION OF THE FACTORY

PT. Schneider Electric Manufacturing Batam
Jl Beringin Lot 4, Lot 208, Lot 1, Lot 15, Lot 16, DAN Lot 16A BIP Muka Kuning Kel.Muka Kuning
Kec. Sungai Beduk – Batam, Indonesia

PRODUCT NAME,MODEL AND SPECIFICATION

Soft Starter

ATS430C14S6 ,ATS430C17S6 ;Uimp:6kV;Ui:600V;Ith: ATS430C14S6:140A, ATS430C17S6:170A;Ue: 208V~600V; Ie:
ATS430C14S6:140A, ATS430C17S6:170A;Pe: ATS430C14S6: 37kW(230V), 75kW(400V), 75kW(440V), 90kW(500V);
ATS430C17S6: 45kW(230V), 90kW(400V), 90kW(440V), 110kW(500V);Utilization Category: AC-53a;pole: 3P

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.6-2016

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jul.19,2024

Valid until: Jul.18,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.

