

en zh






CCT723119



WiFer™

Schneider Electric



en

Wiser IP camera indoor

### Prerequisites

Download the **Wiser app** to your smartphone/tablet.

### Additional system information

Detailed product information is available on-line in the **system user guide**. Scan the QR code or follow the link:



[https://download.schneider-electric.com/files?p\\_Doc\\_Ref=MFR1569800](https://download.schneider-electric.com/files?p_Doc_Ref=MFR1569800)

### Getting to know the product

With the Wiser IP camera indoor (hereinafter referred to as **IP camera**) you can monitor sensitive areas of your home. The IP camera can be triggered by other Wiser devices.

### Installing

You can install the camera in all directions, e.g. on the wall, at the ceiling or on a table.

**i** Observe your local privacy laws. Do not mount the camera in a way that it can monitor public spaces.

### Setting up

You can insert a micro-SD card for local storage. To connect the IP camera to your router, please follow the instructions in the Wiser app.

For more details, refer to the system user guide.

### Resetting

For more details, refer to the system user guide.

### Operating

For more details, refer to the system user guide.

### Technical data

Nominal voltage:	AC 100-240 V, 50/60 Hz
Power adapter PN:	KA12C-0502000BS
Power supply:	DC 5 V, 2 A
Power consumption:	max. 10 W
Operating temperature:	-10 °C - 45 °C
Operating humidity:	<95% RH
Operating Frequency:	2405 - 2480 MHz
Max. radio-frequency power transmitted:	< 100 mW
Wi-Fi® standard:	IEEE 802.11 b/g/n 2.4 GHz
Wi-Fi® security:	WPA-PSK / WPA2-PSK
Channel bandwidth:	Support 20/40 MHz
Data security:	AES128
Resolution:	1080p
Wide angle lens:	80° horizontally 40° vertically
IR range:	7 m
Pan angle:	0° - 340°
Tilt angle:	-75° - 75°
Local storage support:	Micro SD Card, max. 128 GB

### Trademarks


- Wiser™ is a trademark and the property of Schneider Electric SE, its subsidiaries and affiliated companies.
- Wi-Fi® is a registered trademark of Wi-Fi Alliance®.
- Apple® and App Store® are brand names or registered trademarks of Apple Inc.
- Google Play™ Store and Android™ are brand names or registered trademarks of Google Inc.

Other brands and registered trademarks are the property of the relevant owners.

### Schneider Electric Industries SAS

If you have technical questions, please contact the Customer Care Centre in your country.

[se.com/contact](http://se.com/contact)



CCT723119



Wiser™

Schneider Electric

必要條件

下載 Wiser 應用程式到您的智慧型手機 / 平板電腦。

其他系統資訊

詳細的產品資訊可在線上系統使用指南中獲取。掃描 QR 碼或點擊連結：



[https://download.schneider-electric.com/files?p\\_Doc\\_Ref=MFR1569800](https://download.schneider-electric.com/files?p_Doc_Ref=MFR1569800)

瞭解產品

您可以使用 Wiser IP 室內攝影機 (以下簡稱 IP 攝影機) 監視家中的敏感區域。IP 攝影機可由其他 Wiser 設備觸發。

安裝

您可以將攝影機安裝在各種方位, 例如牆上、天花板或桌子上。

請務必遵守當地隱私法。安裝攝影機時, 請勿將攝影機安裝在可監視公共空間的位置。

設定

您可以插入 microSD 卡以進行本地儲存。若要将 IP 攝影機連接至路由器, 請按照 Wiser 應用程式中的說明操作。

請參閱系統使用指南, 獲得更多詳細資訊。

重設

請參閱系統使用指南, 獲得更多詳細資訊。

操作

請參閱系統使用指南, 獲得更多詳細資訊。

技術規格

標稱電壓：	AC 100-240V, 50/60 Hz
電源整流器 PN：	KA12C-0502000BS
電源：	DC 5 V, 2 A
電力消耗：	max. 10 W
工作溫度：	-10 °C - 45 °C
工作濕度：	<95% 相對濕度
工作頻率：	2405 - 2480 MHz
最大射頻功率傳輸：	< 100 mW
Wi-Fi® 標準：	IEEE 802.11 b/g/n 2.4 GHz
Wi-Fi® 安全機制：	WPA-PSK / WPA2-PSK
頻道頻寬：	支援 20/40 MHz
資料加密：	AES128
解析度：	1080p
廣角鏡頭：	水平 80° 垂直 40°
IR 範圍：	7 公尺
平移角度：	0° - 340°
傾斜角度：	-75° - 75°
本地儲存支援：	microSD 卡, 最大容量 128 GB

商標

- Wiser™ 是施耐德電機、其子公司及附屬公司的商標和財產。
- Wi-Fi® 是 Wi-Fi Alliance® 聯盟的註冊商標。
- Apple® 和 App Store® 是 Apple Inc. 蘋果公司的品牌或註冊商標。
- Google Play™ 商店和 Android™ 是 Google Inc. 公司的品牌或註冊商標。

其他品牌和註冊商標為相關所有者的財產。

施耐德電機工業股份有限公司

如果您有任何技術問題, 請聯繫您在國家的客戶服務中心。

se.com/contact

