

What's your pegboard missing?

WARNING

This brochure contains explicit strippers, screwers and cutters.

CLIPSAL[®]
ELECTRICAL ACCESSORIES

Quick Stripper

852QCP

Strip down quicker at work and have more time on your hands for the jobs that matter. With a quick clip, a cable's outer sheath can be easily removed and the conductors made ready for insertion and connection, all with the help of the *Clipsal Quick Connect Pliers*.

In conjunction with the *Clipsal Quick Connect* range, installing power sockets has never been easier. No more stripping, twisting and screwing down conductors on twin power outlets or surface sockets.

The universal design of the Pliers means they have far more use than that of the *Quick Connect* range. The slim line nose will help you get to those hard to reach places. A crimping area and cutters to provide multi-purpose functions, with a non-slip bright coloured grip to easily find when needed the most.

Make the change to **Clipsal Quick Connect Pliers 852QCP** and experience for yourself just how *fast* this tool really is.



Specifically registered designed blade to remove outer sheathing of 1.5mm² and 2.5mm² TPS cable.



STEP 1




STEP 2



STEP 3

For further information contact the Clipsal Brochure Line on 1300 725 547



B



C

D



A

A. 900TC – Mini Trunking/Conduit Cutter

- Multi purpose cutter cuts PVC mini trunking (duct) and conduit
- Conduit range 32mm heavy duty & 40mm light duty
- Handy snap on anvil for cutter available separately (900TCA)
- Replacement blades available (900TCB)
- Bright orange handles for high visibility



900TCA

900TCB

B. 853SK – Four Piece Screwdriver Kit

- Provides the four most commonly used screwdrivers in a convenient pack

Set contains from left to right –



- 250mm flat blade, 6.5mm blade width, insulation diameter 9mm
- 200mm #2 Phillips Head, insulation diameter 9mm
- 225mm flat blade, 5.5mm blade width, insulation diameter 8mm
- 180mm flat blade, 4mm blade width, insulation diameter 7mm
- Fully insulated to 1000V

C. 852LP – Long Nose Pliers

- 175mm length
- Narrow profile head for working in extra tight spaces
- Serrated jaws provide secure gripping surface
- Cutting jaw
- Made from drop-forged alloy steel
- Insulated handles with sure grip cross hatching for complete safety
- Bright orange handles for high visibility

D. 852DC – Diagonal Cutting Pliers

- 200mm length
- Hand honed cutting edges
- High leverage wide opening pivot jaw
- Made from drop-forged alloy steel
- Insulated handles with sure grip cross hatching for complete safety
- Bright orange handles for high visibility



E. 852EP – Insulated Electricians Pliers

- 200mm length
- Hardened cutting jaw cuts through flat multicore & 5 x 2.5mm² orange circular cables
- Cross-hatch jaws provide secure gripping surface
- Serrated pipe grip facility
- Crimper built into handle, for use with non-insulated 1.5-6mm connectors
- Made from drop-forged alloy steel
- Insulated handles with sure grip cross hatching for complete safety
- Bright orange handles for high visibility
- Slim nose appeal for use in tight spaces

F. 852QCP – Insulated Electricians Pliers

- 200mm length
- Registered designed blade to cut through outer sheathing of 1.5 & 2.5mm² 3 core TPS cables
- Extended & hardened cutting jaw cuts through flat multicore & 5 x 2.5mm² orange circular cables
- Serrated jaws provide secure gripping surface
- Crimper built into handle, for use with non-insulated 1.5-6mm connectors
- Made from drop-forged alloy steel
- Insulated handles with sure grip cross hatching for complete safety
- Bright orange handles for high visibility

**852QCP
SHOWN AT
ACTUAL SIZE**



clipsal.com

Products of Gerard Industries Pty Ltd

ABN 27 007 873 529

Head Office

12 Park Terrace, Bowden
South Australia 5007
Telephone (08) 8269 0511
Facsimile (08) 8340 1724
Internet clipsal.com
E-Mail plugin@clipsal.com.au

Offices in all States

NSW Sydney (02) 9794 9200
Albury (02) 6041 2377

VIC Melbourne (03) 9207 3200
Country Areas 1800 653 893

QLD Brisbane (07) 3244 7444
Townsville (07) 4729 3333

SA Adelaide (08) 8268 0400

WA Perth (08) 9442 4444

TAS Launceston (03) 6343 5900

NT Darwin (08) 8947 0278

Area Representatives

NSW Albury (02) 6041 2377
Central Coast 0418 430 361
Coffs Harbour 0418 653 183
Dubbo 0418 822 564
Newcastle 0407 298 792
0418 434 169
0418 686 040

South West Sydney 0419 868 353
Tamworth 0417 714 339
Wagga Wagga 0418 578 903
Wollongong 0418 423 581

ACT Canberra 0419 238 824
Canberra/Goulburn 0418 164 070
Canberra/Yass 0419 847 732

VIC Bendigo 0418 570 213
Geelong 0418 527 233
Gippsland 0418 512 680
Western Victoria 0419 380 444

QLD Cairns 0418 773 254
Gold Coast 0418 765 459
Mackay 0418 752 134
Maryborough 0418 664 338
Northern Rivers 0418 768 902
Rockhampton 0418 794 711
Sunshine Coast 0418 711 786
Toowoomba 0418 726 394
Townsville 0418 180 372

WA Bunbury 0418 931 684
Kalgoorlie & 0417 928 981
Eastern Gold Fields
Karratha 0418 937 249

SA Riverland/Mildura/ 0418 596 145
Broken Hill

**QUICK
CONNECT**

For more information
about Quick Connect
pliers and products call
1300 725 547 for a
free brochure or visit
our website at

clipsal.com



International Enquiries

Head Office Export Department

Telephone + 61 8 8269 0587
Facsimile + 61 8 8340 7350
E-Mail export@clipsal.com.au

New Zealand

Clipsal Industries (NZ) Ltd (Auckland)

Telephone (09) 576 3403
Facsimile (09) 576 1015
E-Mail headoffice@clipsal.co.nz

Customer Service

Free Fax (0508) 250 305
Auckland/Mobile Phone (09) 572 0014
Free Phone (0508) CLIPSAL
2547725

You can find this brochure and many
others online in PDF format at:
clipsal.com

Follow the links off the home page
or access the following page directly:
clipsal.com/wat_lib_pdf.cfm

clipsal.com

Gerard Industries Pty Ltd reserves the right to change specifications, modify designs and discontinue items without incurring obligation and whilst every effort is made to ensure that descriptions, specifications and other information in this catalogue are correct, no warranty is given in respect thereof and the company shall not be liable for any error therein.

©Copyright Gerard Industries Pty Ltd
Printed by Custom Press Pty Ltd (08) 8346 7999

O/N 6807 Dec 03/01