

ML2165 Ultra Plus Series – Plaster Mount Metal Plate - Accessories

ML2165 Accessories (ACC)	
Grid Plates	
2031VH	1 gang grid
2032VH	2 gang grid
2033VH	3 gang grid
2034VH	4 gang grid
2035VH	5 gang grid
2036VH	6 gang grid
Dimmers	
Dimmer Mech	Dimmer Mech - 32 Series
Dimmer	Dimmer - 2031 Series
Mechs	
30M	Switch mech
30P-ID	Circuit ID mech
30P	Plug mech
30RJ	Data and phone socket mech
30TV	TV mech
N01	Power Available Neon
Equipotential Earthing (EP)	
ML2031VR01	Single gang, vertical, EP stud
ML2032VR02	Double gang, vertical, EP stud
ML2031R01	Single gang, horizontal, EP stud
ML2032R02	Double gang, horizontal, EP stud
Single (EP Junction) - ML2165 Plaster Mount EPJ	
ML2164SS-EPJ	EP Junction facia 187mm(H) x 318mm(W) - Suit 4 Module Wall Box

Socket Outlets (GPO-Clipsal)	
Vertical	
2015V	Single gang power outlet, vertical, 250V, 10A
2015VD	Single gang double pole power outlet, vertical, 250V, 10A
2015VXUA	Single gang power outlet, vertical, extra unused aperture, 250V, 10A
2025V	Double gang power outlet, vertical, 250V, 10A
2015D2V	Double gang double pole power outlet, vertical, 250V, 10A
2025VXUA	Double gang power outlet, vertical, extra unused aperture, 250V, 10A
Horizontal	
2015	Single gang power outlet, horizontal, 250V, 10A
2015D	Single gang double pole power outlet, horizontal, 250V, 10A
2015XUA	Single gang power outlet, horizontal, extra unused aperture, 250V, 10A
2025	Double gang power outlet, horizontal, 250V, 10A
2025XUA	Double gang power outlet, horizontal, extra unused aperture, 250V, 10A
Socket Outlets (GPO-Medilec)	
Vertical	
ML2015V	Single gang power outlet, vertical, amber power available neon, RCD label, 250V, 10A
ML2015VI	Single gang power outlet, vertical, amber power available neon, RCD label, circuit identification, 250V, 10A
ML2015-15VI	Single gang power outlet, vertical, amber power available neon, RCD label, circuit identification, 250V, 15A
ML2015VD	Single gang double pole power outlet, vertical, Isolated label, 250V, 10A
ML2015VDI	Single gang double pole power outlet, vertical, Isolated label, circuit identification, 250V, 10A
ML2025V	Double gang power outlet, vertical, amber power available neon, RCD label, 250V, 10A
ML2025VI	Double gang power outlet, vertical, amber power available neon, RCD label, circuit identification, 250V, 10A
ML2025VD	Double gang double pole power outlet, vertical, Isolated label, 250V, 10A
Horizontal	
ML2015	Single gang power outlet, horizontal, amber power available neon, RCD label, 250V, 10A
ML2015I	Single gang power outlet, horizontal, amber power available neon, RCD label, circuit identification, 250V, 10A

ML2015-15I	Single gang power outlet, horizontal, amber power available neon, RCD label, circuit identification, 250V, 15A
ML2015D	Single gang double pole power outlet, horizontal, power neon, Isolated label, 250V, 10A
ML2025	Double gang power outlet, horizontal, amber power available neon, RCD label, 250V, 10A
ML2025I	Double gang power outlet, horizontal, amber power available neon, RCD label, circuit identification, 250V, 10A
RCD	
ML2031VRC10	Single gang double pole, vertical, 250V, 20A, 10mA RCD
ML2031RC10	Single gang double pole, horizontal, 250V, 20A, 10mA RCD
Example Panels	
ML2165 - sample	n/a
Gas Outlets	
<i>ML2165 Plaster Mount Gas Panels – Product Codes for Stainless Steel</i>	
ML2165SS-1E	Single Esco Gas
ML2165SS-2E	Double Esco Gas
ML2165SS-3E	Triple Esco Gas
ML2165SS-4E	Quad Esco Gas
ML2165SS-1C	Single CIG/BOC Gas
ML2165SS-2C	Double CIG/BOC Gas
ML2165SS-3C	Triple CIG/BOC Gas
ML2165SS-4C	Quad CIG/BOC Gas
	(Please contact your local Clipsal representative for powder coat finish)
Alarm	
ML2031VE08	Single gang, vertical, audible/visual alarm, 250V
ML2031E08	Single gang, horizontal, audible/visual alarm, 250V