

## PRODUCT DATA SHEET



### Application:

---

This enclosure is designed for the increased need for the average family household to distribute services such as Free to Air TV, pay TV, DVD, video recorders, surveillance cameras, distributed audio solutions, Internet (wired and wireless versions), data networking and telephone services. Switches, modems and routers can be installed inside the enclosure freeing up space on desks.

This enclosure only comes complete with the following:

- 1 x 10 pair telephone disconnection module and mount
- 1 x communication earthing point
- 1 x Twin Vertical Switched Socket Outlet
- 400mm rubber grommet for cable entries
- fixing screws
- legend card.

### Dimensions:

---

Enclosure – 465mm Wide x 895mm High x 113mm Deep.

## PRODUCT DATA SHEET



## Features:

- reversible door hinging left or right hand side
- same size and look as the 60 pole electrical switchboard (product family)
- multiple cable anchor points
- segregated power zone for 240volt power packs (standards compliant)
- 240 twin Switched Socket outlet and mounting accessories
- long mounting rails for VDU's and other StarServe and audio accessories
- large cable entry above mounting rails for TV cabling (no bending radius issues)
- ample room for StarServe accessories when fully fitted out
- provision for up to 48 Clipsal Keystone Data outlets (Cat 5e or Cat6)
- no bending radius issues for data cabling (Cat 5e or Cat6)
- separate cabling zone for telephone and data cables
- hinged escutcheon for ease of data patch panel termination
- angled escutcheon for patch lead bending radius.

## Accessories Sold Separately:

<b>Data Outlets</b>	Keystone Cat 5e	Keystone Cat 6
	RJ88SMA5,BK	RJ88SMA6,BK
<b>Fast Ethernet Switches</b>	5 Port	8 Port
	95ESW5P10/	95ESW8P10/
<b>Patch Leads</b>	Cat 5e	Cat 6
0.5m	RJ5A8/05PL	RJ6A8/05PL
1.0m	RJ5A8/10PL	RJ6A8/10PL
1.5m	RJ5A8/15PL	RJ6A8/15PL
2.0m	RJ5A8/20PL	RJ6A8/20PL
3.0m	RJ5A8/30PL	RJ6A8/30PL
<b>Switch Bracket / Cradle</b>	3105SWBKT	
<b>VDU - Type</b>	VDU	IR Engine
2 input – 6 output	8072/6VHP	NO
3 input – 8 output	8073/8VHPIR	YES
2 input – 4 output (combination telephone)	3105VDU24T	NO
3 input – 8 output (combination telephone)	3105VDU38IRT	YES
<b>Audio Accessories</b>	Audio Distribution Junction Box	Audio Power supply
	3105ADJB	3105APS24V
<b>Modulator Type</b>	Modulator	IR Distribution
Single Channel Stereo	8071VMS	YES
Single Channel Mono	8071VMP	NO
2 Channel Mono	8072VMPIR	YES
4 Channel Mono	8074VMPIR	YES