



PDL

NEW PRODUCT DATA AND APPLICATION SHEET

CATALOGUE

905BK NT 10A Black
 905CL NT 10A Clear
 905WH NT 10A White
 905LRWH NT Lock-ring 10A White

BARCODE

9416175035906
 9416175035913
 9416175035920
 9416175035937



905/15WH 15A White
 905/15BK 15A Black
 905/15CL 15A Clear
 905RWH Round Earth 10A White
 905RBK Round Earth 10A Black
 905RCL Round Earth 10A Clear

9416175217999
 9416175218002
 9416175219924
 9416175217944
 9416175217951
 9416175217968

925R 10A Black
 925R 10A Clear
 925R 10A White

9416175117176
 9416175117183
 9416175116810

DESCRIPTION

Heavy duty back entry plug and in-line socket



905WH



905/15WH



905RWH



925R

BOX QUANTITY 20

OUTER QUANTITY 200

FEATURES

Available in clear, white and black.
 Plugs available in 10A, 15A, and Round Earth versions.
 Sheathed plug pins.
 Plugs have new terminal design and layout for ease of termination.
 Plug terminals incorporate a clamping design for positive and fast termination.
 New serrated terminals provide further assistance for gripping conductors during termination.
 New plug terminal screws, combination No1 phillips/slot screws.
 Captivated fixing screws from base to cover.
 Hinged cord clamp design to swing out of the way during termination.
 All wires are clamped between two flat surfaces for maximum effect.
 In-line socket is shrouded to comply with regulations.
 Polycarbonate bodies for both plug and in-line socket for long life.
 Moulded finger grip surfaces for easy insertion and withdrawal.



P D L

NEW PRODUCT DATA AND APPLICATION SHEET

Clear, indelible markings for all terminals. Earth terminal printed green.

SPECIFICATIONS 905, 905R, and 925R -10A rating at 230-240V ac, 50Hz.
905/15 – 15A rating at 230-240V ac, 50Hz
Terminals accommodate conductors from 0.75mm² to 1.5mm².
Recommended for use with PVC insulated ordinary duty 3 core circular flexible cords.
Recommended stripping length equals 40mm, including 8.5mm bare wires.
Complies with AS/NZS3112 and AS/NZS3100
In line socket approval number V/910236.
Plug has regulations approval number V/910237.

APPLICATIONS Standard 10A plug and in-line socket use. 15A and round earth plug options for specialist appliances and areas of use. Clear products allow visible check of wires and terminals which is a requirement in certain applications.

COMMENTS Other items in the 900 Series range include: Cat 901 Side Entry Plug, 10A, 15A; Cat 903 Hook Grip Side Entry Plug, 10A; Cat 940 Side Entry Tapon Plug, 10A; Cat 927 and 927P Switched Pendant Connector, 10A; Cat 593LRP Flush Socket with Plug; Cat 976P Range Plug 32A;

Features Illustrated:

- new terminals,
- new terminal screws,
- hinged cord clamp,
- sheathed plug pins.

