



Commercial status

End of Commercialisation : JUN 30, 2023

 End of Commercialisation

Main

Range	Lisse
Aesthetic name	Screwless deco
Product or component type	Dimmer
Device presentation	Complete product
Load type	230 V AC LED lamp: 5...100 W Incandescent lamp: 25...100 W Halogen lamp: 25...100 W
Colour tint	Satin brass
Quantity per set	Set of 1

Complementary

Device mounting	Wall mounted
Dimmer application	Inductive load Resistive load
[Ue] rated operational voltage	230 V AC 50 Hz
Number of gangs	1 gang
Material	Stainless steel
Connections - terminals	Screw terminals
Fixing mode	Concealed screws
Type of packing	Bag
Height	87 Mm
Width	87 Mm
Depth	44 Mm
Net weight	0.129 Kg

Environment

Standards	BS EN 60669-2-1
IP degree of protection	IP20

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 Cm
Package 1 Width	8.7 Cm
Package 1 Length	8.7 Cm
Package 1 Weight	144 G
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	9.8 Cm
Package 2 Width	10 Cm
Package 2 Length	25 Cm
Package 2 Weight	798.2 G
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	22 Cm
Package 3 Width	52 Cm
Package 3 Length	52 Cm
Package 3 Weight	16.795 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **End of commerc. - Block**