

No. P23226998

Applicant	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92500 Rueil-Malmaison France
Manufacturer	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92500 Rueil-Malmaison France
Factory	Schneider Electric Elda S.A. ul. Bugno 1 Szczecinek PL-78.400 Poland
Project Number	PRJ0034180
Product	Socket-outlet
Model/Type Ref.	101414
Ratings	16A 250V~
Trademark	Schneider Electric
Principal Characteristics	Class I and II, IP20, IP44 Standard sheet I, III, and I: NF C 61-314:2017
A sample of the product was tested and found to be in conformity with	Safety IEC 60884-1:2002, IEC 60884-1:2002/AMD1:2006, IEC 60884-1:2002/AMD2:2013 NEK 502:2016;A1
Validity	This certificate documents conformity with the standards shown, and also applies as license for use of Nemko's name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.
Additional Information	Revirable Socket-outlets, Schuko-type, with shutters, screw- or screw-less terminals available, IP-Classes: 20 and 44. and Revirable Socket-outlets, 2P with Pin-type Protective Earth, Screw-type terminals, with shutters. Available as IP20.and Revirable Socket-outlets, 2P without Protective Earth, flush-type, with shutters, screw- or screw-less terminals available, Available as IP20. General: In case the socket-outlet with unearthed fixing frame or plastic frame is to be installed in a metal box, the insulation p/n: BBV49557 shall be installed. In case the socket-outlet with earthed fixing frame is to be installed in a metal box (box earthed) a clearance of minimum 3 mm shall be met. This certificate replaced previous certificate No. P23226752, due to standard update.
Additional model(s)	(2) See page 2

Jiyea Gim

Jiyea Gim
Certification Department
12 / 04 / 2023



www.nemko.com

Page 1 of 6



CERTIFICATE

No. P23226998



Product	Socket-outlet
Variant No.	1
Model/Type Ref.	101414-02
Ratings	16A 250V~
Trademark (if different from page 1)	
Principal Characteristics	Class I and II, IP20, IP44 Standard sheet I, III, and I: NF C 61-314:2017
Product	Socket-outlet
Variant No.	2
Model/Type Ref.	101443-02
Ratings	16A 250V~
Trademark (if different from page 1)	
Principal Characteristics	Class I and II, IP20, IP44 Standard sheet I, III, and I: NF C 61-314:2017

Jiyea Gim

Signature

Jiyea Gim

Date of issue

Certification Department
12 / 04 / 2023



www.nemko.com

Page 2 of 6

Appendix

SideE socket-outlets available build of parts:

Part	Description
101414-02	insert base (Renova screw, Round screw)
101443-02	insert base (Exxact, Trend, Robust, Unica, new Unica, Odace, Ovalis)
101414	insert base (Exxact IP44 surface screwless / flush screw)
100977	insert cover & fixing part, screw-type (Exxact IP44), nature
101081	insert cover (Round), white
101366	insert cover & fixing part, screw-type, nature (Unica, Renova)
101415	insert cover (screw)(Exxact, Unica, Odace, Ovalis, Robust, Trend, Unica new)
101421	insert cover (screw + screwless) (Exxact)
101430	insert cover (screwless)(Exxact, Trend, System M, System Design, Robust)
100594	shutter slider natural / black
101037	shutter cassette body
101164	surface box (Exxact IP44), white
101164	surface box (Exxact IP44), black
101165	center plate SideE (Exxact IP44), white
101165	center plate SideE (Exxact IP44), black
101166/101167	lid (Exxact IP44), white
101166/101167	lid (Exxact IP44), black
101155	center plate SideE (Round), white
101367, 101364	center plate SideE (Renova), white
101367, 101364	center plate SideE (Renova), black
101392	center plate SideE (Trend)
101527	center plate SideE (Unica)

Jiyea Gim

Signature

Jiyea Gim

Date of issue

Certification Department
12 / 04 / 2023



www.nemko.com

Page 3 of 6

Working for a more sustainable future- Please do not print

101531	center plate SideE (Unica)
101604	center plate SideE (Robust surface)
101610	center plate SideE (Robust flush)
BBV35087	center plate SideE (Exxact high, full-flush), white
BBV35087	center plate SideE (Exxact high, full-flush), black & black + painted
BBV35087	center plate SideE (Exxact low, semi flush), white
BBV35087	center plate SideE (Exxact low, semi flush), black & black + painted
BBV11157	center plate SideE (Exxact), white
BBV4013402	center plate SideE (Odace), white / + painted alu
BBV42390	center plate SideE (Exxact), white
NHA44968	center plate SideE (M-SMART, full-flush), white
NHA44968	center plate SideE (M-SMART, full-flush), active white & ivory
NHA44972	center plate SideE (M-SMART, semi flush), white
NHA44972	center plate SideE (M-SMART, semi flush), active white & ivory
S1A67876	center plate SideE (Exxact), white / painted met or anthr.
S1B13009	center plate unearthed / SideE (Exxact), white
BBV49557	Insulation

Jiyea Gim

Signature

Date of issue

Jiyea Gim

Certification Department

12 / 04 / 2023

Working for a more sustainable future- Please do not print



www.nemko.com

Page 4 of 6

PinE socket-outlets available build of parts:

Part	Description
101414-02	insert base (Renova screw, Round screw)
101443-02	insert base (Exxact, Trend, Robust, Unica, new Unica, Odace, Ovalis)
101081	insert cover (Round)
101366	insert cover & fixing part, screw-type, nature (Unica, Renova)
101415	insert cover (screw) (Exxact, Unica, Odace, Ovalis, Robust, Trend, Unica new)
100594	shutter slider natural / black
101037	shutter cassette body
101530	center plate PinE PO/FR (Unica)
101533	center plate PinE CZ (Unica)
101535	center plate PinE CZ (Unica)
NVE8058402	center plate PinE FR (new Unica), white / painted alu/ graphite
S1A6508002	center plate PinE FR (Ovalis), white
BBV5354402	center plate PinE FR (Odace), white / + painted alu
BBV49557	Insulation

Jiyea Gim

Signature

Jiyea Gim

Date of issue

Certification Department

12 / 04 / 2023

Working for a more sustainable future- Please do not print



www.nemko.com

Page 5 of 6

Unearthed socket-outlets available build of parts:

Part	Description
101414-02	Insert base
101443-02	Insert base
101366	insert cover & fixing part, screw-type, nature (Unica, Renova)
101415	insert cover (screw) (Exxact, Unica, Odace, Ovalis, Robust, Trend, Unica new)
101430	insert cover (screwless) (Exxact, Trend, System M, System Design, Robust)
100594	shutter slider natural / black
101037	shutter cassette body
BBV49557	Insulation
100465	center plate unearthed (Trend)
101528	center plate unearthed (Unica)
101365, 101364	center plate unearthed (Renova)
101532	center plate unearthed (Unica)
BBV42385	center plate unearthed (Exxact)
S1B13009	center plate unearthed / SideE (Exxact)



Jiyea Gim
Certification Department
12 / 04 / 2023



www.nemko.com

Page 6 of 6

Signature

Date of issue