





3025CSG  
PDL395CSG

WiZer™

Schneider  
Electric



NNZ58572

## en Iconic Connected Socket Twin 10 A

### About this product

The Iconic Connected Socket Twin 10 A operates as a standard socket outlet "out-of-the-box", with no configuration needed. The socket is available with Bluetooth connectivity.

The socket can be paired to a mobile phone and the Wisier by SE app. In this case, the socket can be operated remotely and optionally configured with a delay timer and a scheduler function.

### 1 Product details

- A Rocker switch
- B Touch switch

### Mounting and Connections

#### ⚠️ ⚠️ DANGER

#### HAZARD OF ELECTRIC SHOCK, OR ARC FLASH

- It is illegal for persons other than an appropriately licensed electrical contractors or other persons authorised by legislation to work on the fixed wiring of any electrical installation.
- To comply with all safety standards, the device must be used only for the purpose described in this instruction and must be installed in accordance with the wiring rules and regulation in the location where it is installed.
- Lock out and tag the input circuit before accessing the wiring connections.
- There are no user serviceable parts inside the device

**Failure to follow these instructions will result in death or serious injury.**

#### ⚠️ CAUTION

#### EQUIPMENT DAMAGE HAZARD

- Install the device according to instructions in this document.
- Pay attention to the specifications and wiring diagrams related to the installation.
- Do not use the device for any other purpose than specified in this instruction.
- Dropping the device may damage the socket. Check that the device operates after being dropped or if physical damage is shown.

**Failure to follow these instructions can result in minor injury or equipment damage.**

### 2 Reading the full device user guide online

Scan the QR code for complete information about the device, including operation, configuration and using the product.

### Technical data

|   |   |
|---|---|
| Operating voltage                       | 240 V AC 50 Hz  |
| Max. load rating                        | 10 A  |
| LED indicator                           | Yes   |
| Technology type                         | Bluetooth low energy  |
| Operating frequency:                    | 2.405 GHz to 2.48 GHz   |
| Max. radio-frequency power transmitted: | 10 mW at < 50 m   |
| Compatible wall box and bracket ranges  | 155<br>155NA<br>157<br>157PRM<br>157/1PRMD<br>157/1F<br>PDL144M<br>PDL144P<br>PDL140F |
| Compliance                              | Safety: AS/NZS 3112<br>AS/NZS 60669.2.1<br>EMC: AS/NZS 60669.2.1<br>RF: AS/NZS 4268   |
| Power failure data retention            | Internal date/time retained for at least 6 hrs. Settings preserved indefinitely.      |
| Environmental rating                    | IP20 (designed for indoor use only)   |
| Operating humidity                      | 5 %–90 % relative humidity, non-condensing  |
| Specifications typical at 25 °C         |   |

### Trademarks

- Bluetooth® is a registered trademark owned by Bluetooth SIG, Inc.
  - Wisier is a trademark and the property of Schneider Electric, its subsidiaries and affiliated companies.
- Other brands and registered trademarks are the property of their respective owners.

### Customer Care

#### Warranty information

We warrant this product for 2 years. See Warranty links below.

#### Schneider Electric (Australia) Pty Ltd

33-37 Port Wakefield Road, Gepps Cross SA 5094

Customer Care: 13 73 28

Email: [customercare.au@se.com](mailto:customercare.au@se.com)

Warranty: <https://www.clipsal.com/warranty>

[www.clipsal.com](http://www.clipsal.com)

#### Schneider Electric (NZ) Ltd

Level 2, Building 6, 60 Highbrook Drive

Highbrook, Auckland 2013

Customer Care: 0800 652 999

Email: [sales@nz.schneider-electric.com](mailto:sales@nz.schneider-electric.com)

Warranty: <https://www.se.com/nz/en/about-us/legal/terms-and-conditions.jsp>

[www.pdl.co.nz](http://www.pdl.co.nz)