

# CLIPSAL®

by Schneider Electric

## 56FA Series Flush Surrounds


### 56FA Series

Mounting Details

**56FA Series pack includes M3.5 x 40mm screws, moulded surround and gasket**

#### Typical 56 Series Module

**Note:** Remove cover mounting screws and replace with M3.5 x 40mm screws supplied with flange assembly.



#### 56FA Moulded Surround



#### Gasket



**Note:** Mounting brackets to suit 56FA Series are sold separately.

#### 56E Enclosure

**Note:** Ensure top edge of enclosure is fitted as close as possible to finished wall face.

Mounting Bracket  
(if required)




## Poured Concrete Walls (Enclosure Mounting)

Position enclosure at correct height on formwork. Pour concrete over the enclosure.

**Note:** To prevent conduit entry obstructions, appropriately seal conduit prior to pouring concrete.

Adhere gasket to flange and mount 56 Series modules to enclosure through flange when concrete is fully cured.




## Solid and Cavity Brick Walls (Bracket Mounting)

Prepare wall by cutting hole 90 x 90mm for 56FA1, 90 x 190mm for 56FA2, 90 x 285mm for FA3 and 190mm<sup>2</sup> for 56FA4. Mount bracket to exterior wall using any suitable fixing device; i.e. thru-bolts, fibre plugs, etc.

Remove adhesive backing sheet from gasket and adhere to inner surface of flange. Mount modules to bracket through flange.

**Note: 1.** For soft or porous brickwork we suggest adhesive anchored fixing.


**2.** When mounting to brick ensure all mortar joints are sealed with suitable caulking compound.



## Panel Type Walls (Bracket Mounting)

Prepare wall by cutting hole as described above for solid and cavity brick walls. Mount bracket to wall using suitable hollow wall anchors. Adhere gasket to flange and mount modules through flange to bracket.

**Note:** If possible mount bracket to building frame; i.e. wooden nogginns and studs with suitable wood screws.



## Clipsal Australia Pty Ltd

A member of Schneider Electric

[clipsal.com](http://clipsal.com)

Contact us: [clipsal.com/feedback](http://clipsal.com/feedback)

National Customer Care Enquiries:

**Tel 1300 2025 25 Fax 1300 2025 56**

Clipsal Australia Pty Ltd reserves the right to change specifications, modify designs and discontinue items without incurring obligation and whilst every effort is made to ensure that descriptions, specifications and other information in this catalogue are correct, no warranty is given in respect thereof and the company shall not be liable for any error therein.

© Clipsal Australia Pty Ltd. The identified trademarks and copyrights are the property of Clipsal Australia Pty Ltd unless otherwise noted.

F062/03, 309958

CLIPCOM 21084 May 2010