


# The all in one system for effective protection and load control

## > Acti 9 Reflex iC60

Integrated control circuit breaker  
Overview guide



Acti 9: The efficiency you deserve



# Reflex iC60

The all-in-one integrated control circuit breaker

A complement to the Acti 9™ system and exclusive to Schneider Electric, the Reflex iC60 combines an MCB (miniature circuit breaker) with an internal actuator. Designed to evolve and adapt with the dynamic requirements of tertiary and industrial lighting control applications, it easily communicates with PLCs without the need for add-ons, retrofits or extras. It is especially dedicated to the load remote management of tertiary buildings & industrial plants which combine local control and centralised control with a number of switching operations.

**Ti24 interface**  
for connection to Acti 9 Smartlink or PLC

**ComReady**

Available only from Schneider Electric

**3 operating modes**  
for all applications

**Integrated padlocking**  
for complete safety

**Integrated signalisation**

**Latched and impulse orders**

**VisiSafe**

**Protection**  
against short circuits and overloads

'With the Reflex iC60 we saved 15 percent on our energy use, due to its simplified control of lighting circuits. Normal lighting is controlled remotely by the controller (PLC) based on periods of activity and selected lighting. As a result, daily control of our loads is simple. Installation was easy; the 'all in one' concept reduced power terminal wiring by 50 percent. Plus, the Reflex iC60 allows direct connection to the PLC without any low current interfaces'.

H. Rascon, building technician



**25%**

space savings due to all in one design

**24 V**

direct connection to PLC or BMS

**100%**

coordination between MCB and actuator

'Thanks to the Reflex iC60 we can manage control lighting of our office buildings in a totally safe installation'

H. Richard - electrician

## Complete safety

### For the installation:

- > VisiSafe inside with Uimp 6 kV, pollution degree level 3, Ui 500V
- > Compliant with IEC 60947-2 as well as major quality standards
- > Fast closing mechanism protects the load and guarantees long service life

### For the operator:

- > Class 2 front face for absolute protection
- > Integrated padlocking for complete lock down



Integrated padlocking device for complete safety and lockdown capabilities



Reflex easily connects to Modbus network through Acti 9 Smartlink

**ComReady**



Reflex iC60 is part of the Acti 9 communication and control system

## Efficient

### Continuity of service:

- > Bi-stable operation maintains stable status

### Simplified maintenance:

- > Front face indicator allows better readability during maintenance and fault diagnosis

## Simple and smart

### Easy to design

- > An all-in-one solution which complies with all lighting application requirements
- > Connection to PLC via Ti24 interface
- > Flexible control orders for late differentiation

### Easy to choose

- > Quick and reliable connection to Acti 9 Smartlink via prefabricated cables
- > Wide range up to 40 A

### Easy to install

- > Saves switchboard space by up to 25%
- > Up to 50 percent reduction of power connections and 70 percent on control wiring, with faster wiring tests



## Low-voltage distribution


Industrial and infrastructure load shedding applications



## Lighting control

Exterior, interior, remote street lighting control and operation

# Ready to be connected



The Reflex iC60 is the perfect all-in-one solution for remote load management of tertiary buildings, industrial plants and interior and exterior public infrastructure lighting applications.

## Offer overview

### Current ratings

- > 10 A, 16 A, 25 A, 40 A

### Breaking capacity


- > Reflex iC60H: 15 kA

### Tripping curves

- > C, D

### Control voltages

- > 230 V AC + 24 V DC (Ti24 versions)



**Make the most of your energy<sup>SM</sup>**

## Schneider Electric Ltd

United Kingdom  
Stafford Park 5,  
Telford  
Shropshire  
TF3 3BL  
Tel: 0870 608 8 608  
Fax: 0870 608 8 606  
www.schneider-electric.com/uk

Ireland  
Head office,  
Block a  
Maynooth Business Campus  
Maynooth, Co. Kildare  
Tel: (01) 601 2200  
Fax: (01) 601 2201  
www.schneider-electric.com/ie

Schneider Electric Limited is a company registered in England and Wales.  
Registered number: 1407228. Registered office: Stafford Park 5, Telford, Shropshire TF3 3BL.

© 2011 Schneider Electric. All Rights Reserved. Schneider Electric, Active Energy Management, Compact, EcoStruxure, ION Enterprise, iRIO, Make the most of your energy, Masterpact, Micrologic, Power Plant To Plug, Modbus, and PowerLogic are owned by Schneider Electric Industries SAS, or its affiliated companies in the United States and other countries. 998-3432.

As standards, specifications and designs change from time to time, please ask for confirmation of the information given in this publication.

member of



**Schneider**  
Electric<sup>SM</sup>