


PDU Multi-Branch Cordset Adapters Installation and Specifications

APC offers three Multi-Branch Cordset Adapters. The adapters connect to a multi-branch power cord on the InfraStruXure PDU, and distribute three separate branches to Rack PDUs in your equipment racks. See the tables beginning on this page for compatible APC Rack PDUs.



Compatible APC 120V PDUs				
PDU#	Plug	Outlets	Manageable	
AP7530	L5-20P	(24) NEMA 5-20R	No	
AP9551	L5-20P	(14) NEMA 5-15R	No	
AP9563	5-20P	(10) NEMA 5-20R	No	
AP9564	L5-20P	(10) NEMA 5-20R	No	
AP7830	L5-20P	(24) NEMA 5-20R	Yes	
AP7901	L5-20P	(8) NEMA 5-20R	Yes	
AP7930	L5-20P	(24) NEMA 5-20R	Yes	
AP7930J	L5-20P	(24) NEMA 5-15R	Yes	
AP9510520	5-20P	(2) NEMA 5-20R	Yes	
SU042X163	L5-20P	(1) NEMA L5-20R	No	


Compatible APC 208V PDUs				
PDU #	Plug	Outlets	Manageable	
AP7540	L6-20P	(20) IEC 320 C13 (4) IEC 320 C19	No	
AP7840	L6-20P	(20) IEC 320 C13 (4) IEC 320 C19	Yes	
AP7940	L6-20P	(21) IEC 320 C13 (3) IEC 320 C19	Yes	
AP9510L620	L6-20P	(1) NEMA L6-20R	Yes	
SU045X163	L6-20P	(1) NEMA L6-30R	No	

How to use the multi-branch cordset adapters



Use the multi-branch cordset adapters with an InfraStruXure system. Connect a multi-branch cordset adapter's plug only to an InfraStruXure PDU power cord.


Connect the plug of the multi-branch cordset adapter to the receptacle of an InfraStruXure PDU power cord in an InfraStruXure Shielding Trough.




Connect each of the three receptacles on the multi-branch cordset adapter to a different APC Rack PDU. See the tables beginning on the previous page for compatible APC Rack PDUs.

Specifications


AP9882



AP9883



AP9884





APC Worldwide Customer Support

Customer support for this or any other APC product is available at no charge in any of the following ways:

- Visit the APC Web site to access documents in the APC Knowledge Base and to submit customer support requests.
 - www.apc.com (Corporate Headquarters)

Connect to localized APC Web sites for specific countries, each of which provides customer support information.

– www.apc.com/support/

Global support searching APC Knowledge Base and using e-support.

- Contact an APC Customer Support center by telephone or e-mail.
 - Regional centers:

Direct InfraStruXure Customer Support Line	(1)(877)537-0607 (toll free)	
APC headquarters U.S., Canada	(1)(800)800-4272 (toll free)	
Latin America	(1)(401)789-5735 (USA)	
Europe, Middle East, Africa	(353)(91)702000 (Ireland)	
Japan	(0) 35434-2021	
Australia, New Zealand, South Pacific area	(61) (2) 9955 9366 (Australia)	

Local, country-specific centers: go to www.apc.com/support/contact for contact information.

Contact the APC representative or other distributor from whom you purchased your APC product for information on how to obtain local customer support.

Entire contents copyright © 2004 American Power Conversion. All rights reserved. Reproduction in whole or in part without permission is prohibited. APC, the APC logo, and InfraStruXure are trademarks of American Power Conversion Corporation and may be registered in some jurisdictions. All other trademarks, product names, and corporate names are the property of their respective owners and are used for informational purposes only.



