


- NOTES:
1. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
  2. NET WEIGHT IS 12 LBS [5.5kg]
  3. UNIVERSAL MOUNTING BRACKET IS AN ALTERNATIVE MOUNTING METHOD TO THE TOOLLESS MOUNT FOR NON APC RACKS.
  4. BRACKET KITS TO MOUNT TO SPECIFIC COMPETITORS RACKS ARE AVAILABLE AS OPTIONS.
  5. INSTALLATION MUST COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL CODES.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF AMERICAN POWER CONVERSION AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM APC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.		TITLE: RACK PDU, BASIC ZERO U, 5.7kW, 120 & 208V, INPUT:NEMA L21-20P OUTPUT: (21)NEMA 5-20R & (6)NEMA L6-20R MAIN MECHANICAL	DWG NO: AP7563-MM1	REV: 1	 AMERICAN POWER CONVERSION 132 FAIRGROUNDS RD WEST KINGSTON, RI 02892
PROJECT: SUBMITTAL DRAWINGS	SHEET 1 OF 2	CHECKED BY: T.HORSTMANN	09/22/05	09/22/05	
		ENGINEER: J.RING/ E.SILVA	09/22/05	09/22/05	

# ISOMETRIC VIEW



THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF AMERICAN POWER CONVERSION AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM APC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

TITLE:	RACK PDU, BASIC ZERO U, 5.7kW, 120 & 208V, INPUT:NEMA L21-20P
OUTPUT:	(21)NEMA 5-20R & (6)NEMA L6-20R ISOMETRIC VIEW
PROJECT:	SUBMITTAL DRAWINGS SHEET 2 OF 2

DWG NO:	AP7563-MM2	REV:	1
DRAWN BY:	JAYAPRAKASH		09/22/05
CHECKED BY:	T.HORSTMANN		09/22/05
ENGINEER:	J.RING/ E.SILVA		09/22/05

**APC**<sup>®</sup>  
 AMERICAN POWER CONVERSION  
 132 FAIRGROUNDS RD  
 WEST KINGSTON, RI 02892