



## Main

Range compatibility	Altivar Process 600/900
Accessory / separate part type	Fan kit
Accessory / separate part category	Cooling accessory
Product or component type	Fan
Net weight	1.34 Kg

## Complementary

Kit composition	Fan Mounting bracket Instruction sheet
Product compatibility	Variable speed drive ATV630 floor-standing 110 kW 380...440 V Variable speed drive ATV630 floor-standing 132 kW 380...440 V Variable speed drive ATV630 floor-standing 160 kW 380...440 V Variable speed drive ATV630 floor-standing 200 kW 380...440 V Variable speed drive ATV630 floor-standing 250 kW 380...440 V Variable speed drive ATV630 floor-standing 315 kW 380...440 V Variable speed drive ATV650 floor-standing 110 kW 380...440 V Variable speed drive ATV650 floor-standing 132 kW 380...440 V Variable speed drive ATV650 floor-standing 160 kW 380...440 V Variable speed drive ATV650 floor-standing 200 kW 380...440 V Variable speed drive ATV650 floor-standing 250 kW 380...440 V Variable speed drive ATV650 floor-standing 315 kW 380...440 V Variable speed drive ATV930 floor-standing 110 kW 380...440 V Variable speed drive ATV930 floor-standing 132 kW 380...440 V Variable speed drive ATV930 floor-standing 160 kW 380...440 V Variable speed drive ATV930 floor-standing 200 kW 380...440 V Variable speed drive ATV930 floor-standing 250 kW 380...440 V Variable speed drive ATV930 floor-standing 315 kW 380...440 V Variable speed drive ATV950 floor-standing 110 kW 380...440 V Variable speed drive ATV950 floor-standing 132 kW 380...440 V Variable speed drive ATV950 floor-standing 160 kW 380...440 V Variable speed drive ATV950 floor-standing 200 kW 380...440 V Variable speed drive ATV950 floor-standing 250 kW 380...440 V Variable speed drive ATV950 floor-standing 315 kW 380...440 V

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 Cm
Package 1 Width	11.0 Cm
Package 1 Length	10.0 Cm

Package 1 Weight	1.336 Kg
Unit Type of Package 2	S04
Number of Units in Package 2	3
Package 2 Height	30.0 Cm
Package 2 Width	40.0 Cm
Package 2 Length	60.0 Cm
Package 2 Weight	5.23 Kg

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**