



Square D™ Mono-Flat Covers

A new high-end alternative
for load center covers

Unique features

- Aesthetically pleasing design for all load center applications
- Low profile surface cover with concealed hardware, trim mounting screws and door hinges
- Easy to install utilizing the EZ hang bracket
- Double door latches standard on 60 space load center covers
- Deadfront design makes servicing load center easier
- Available in gray and white for QO™ load centers and gray only for Homeline™ load centers
- Type 1
- Field installable lock kit available, order catalog number PK4FL



Life Is On

SQUARE D™
by Schneider Electric

Specifications

Covers for QO Load Centers

| Catalog number | Spaces | Color | Mechanical specs | |
|----------------|--------|-------|-----------------------|----------------------|
| | | | W x H x D (mm) | W x H x D (in) |
| QOCMF30UC | 30 | Gray | 394.2 x 797.1 x 26.4 | 15.52 x 31.38 x 1.04 |
| QOCMF30UCW | 30 | White | 394.2 x 797.1 x 26.4 | 15.52 x 31.38 x 1.04 |
| QOCMF42UC | 42 | Gray | 394.2 x 1003.6 x 26.4 | 15.52 x 39.51 x 1.04 |
| QOCMF42UCW | 42 | White | 394.2 x 1003.6 x 26.4 | 15.52 x 39.51 x 1.04 |
| QOCMF54UC | 54 | Gray | 394.2 x 1029.2 x 26.4 | 15.52 x 40.52 x 1.04 |
| QOCMF54UCW | 54 | White | 394.2 x 1029.2 x 26.4 | 15.52 x 40.52 x 1.04 |
| QOCMF60UC | 60 | Gray | 394.2 x 1081.8 x 26.4 | 15.52 x 42.59 x 1.04 |
| QOCMF60UCW | 60 | White | 394.2 x 1081.8 x 26.4 | 15.52 x 42.59 x 1.04 |

Covers for QO Wide Gutter Load Centers

| Catalog number | Spaces | Color | Mechanical specs | |
|----------------|--------|-------|-----------------------|----------------------|
| | | | W x H x D (mm) | W x H x D (in) |
| NQC20FWG | 20 | Gray | 394.2 x 561.34 x 26.4 | 15.52 x 22.10 x 1.04 |
| NQC20FWGW | 20 | White | 394.2 x 561.34 x 26.4 | 15.52 x 22.10 x 1.04 |
| NQC30FWG* | 30 | Gray | 394.2 x 788.41 x 26.4 | 15.52 x 31.04 x 1.04 |
| NQC30FWGW* | 30 | White | 394.2 x 788.41 x 26.4 | 15.52 x 31.04 x 1.04 |

Covers for Homeline Load Centers

| Catalog number | Spaces | Color | Mechanical specs | |
|----------------|--------|-------|-----------------------|----------------------|
| | | | W x H x D (mm) | W x H x D (in) |
| HOMCMF60UC | 60 | Gray | 394.2 x 1273.6 x 26.4 | 15.52 x 50.14 x 1.04 |

Accessories

| Catalog number | Description |
|----------------|---------------|
| PK4FL | Door Lock Kit |

*CANNOT be used when panel has been converted to main circuit breaker panel.



QOMF42UCW



QOMF42UC

Mono-Flat Covers

Simple Installation

1. Install Mounting Brackets



2. Install Deadfront




3. Mount Trim with EZ-hang bracket



4. Install Trim Screws



5. Installation Complete



Life Is On

SQUARE DTM
by Schneider Electric

Boston One Campus
800 Federal Street
Andover, MA 01810

© 2020 Schneider Electric. All Rights Reserved. Schneider Electric, Life Is On Schneider Electric, Square D, Homeline, and QO are trademarks and the property of Schneider Electric, its subsidiaries, and affiliated companies. All other trademarks are the property of their respective owners.
• 998-2085541_US