

# Product data sheet


## Characteristics

# AK2CA6

## Cover for cable duct - Width=60mm

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 23.60 USD



### Main

Product or Component Type	Cover
Accessory / separate part categor	Cabling accessories
Range compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Mounting support	Cable duct 2.36 in (60 mm)
Quantity per Set	Set of 8

### Complementary

Color	Blue RAL 5000)
Length	78.74 In (2000 mm)
Width	2.36 In (60 mm)
Material	PVC (polyvinyl chloride)
Net Weight	0.95 Lb(US) (0.43 kg)

### Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 VDE 0660

### Ordering and shipping details

Category	US1000I22622
Discount Schedule	000I
GTIN	3389110570267
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.39 In (1.0 cm)
Package 1 Width	3.94 In (10.0 cm)
Package 1 Length	78.74 In (200.0 cm)
Package 1 Weight	16.12 Oz (457.0 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	1120
Package 2 Height	42.52 In (108.0 cm)
Package 2 Width	79.13 In (201.0 cm)
Package 2 Length	47.24 In (120.0 cm)
Package 2 Weight	1316.16 Lb(US) (597.0 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	8
Package 3 Height	79.13 In (201.0 cm)
Package 3 Width	4.53 In (11.5 cm)
Package 3 Length	2.56 In (6.5 cm)
Package 3 Weight	8.91 Lb(US) (4.04 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**