

# Product data sheet


## Characteristics

# AK2GA69

Cable duct - 90 x 60 mm - without cover - blue

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 22.00 USD



### Main

Product or Component Type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device Composition	Without cover
Quantity per Set	Set of 8

### Complementary

Color	Blue RAL 5000)
Fixing Mode	Clip-on support By screws
Material	PVC (polyvinyl chloride)
Height	3.54 In (90 mm)
Length	78.74 In (2000 mm)
Width	2.36 In (60 mm)
Net Weight	2.65 Lb(US) (1.2 kg)
Total number of wires	400

### Environment

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	NF C 68-102 VDE 0506 VDE 0660 DIN 43659

## Ordering and shipping details

Category	US1000I22622
Discount Schedule	000I
GTIN	3389110570564
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.28 In (18.5 cm)
Package 1 Width	5.71 In (14.5 cm)
Package 1 Length	84.65 In (215 cm)
Package 1 Weight	32.31 Oz (916 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	7.28 In (18.5 cm)
Package 2 Width	5.71 In (14.5 cm)
Package 2 Length	78.74 In (200 cm)
Package 2 Weight	17.64 Lb(US) (8 kg)
Unit Type of Package 3	P2M
Number of Units in Package 3	304
Package 3 Height	47.24 In (120 cm)
Package 3 Width	79.13 In (201 cm)
Package 3 Length	40.55 In (103 cm)
Package 3 Weight	1463.87 Lb(US) (664 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**