



Commercial status

End-of-Sale Notice : OCT 15, 2024

End-of-Sale Notice

Main

Range	Acti9
Product or component type	OC contact
Device short name	OF
Signal contacts composition	1 C/O
[In] rated current	AC-12 3 A at 380...415 V, AC 50/60 Hz AC-12 6 A at 220...240 V, AC 50/60 Hz DC-12 1 A at 130 V, DC DC-12 1.5 A at 60 V, DC DC-12 2 A at 48 V, DC DC-12 6 A at 24 V, DC
[Uc] control circuit voltage	24...415 V AC 50/60 Hz 24...130 V DC
9 mm pitches	1
Standards	EN/IEC 60947-5-1
Product certifications	ASEFA[RETURN]KEMA[RETURN]LCIE[RETURN]ASTA

Complementary

Mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top: YES
Height	85.3 Mm
Width	9 Mm
Depth	73.5 Mm
Net weight	30 G
Colour	White
Connections - terminals	Screw clamp terminal (bottom) 2 cable(s) 1.5 mm ² - flexible Screw clamp terminal (bottom) 1 cable(s) 0.5...2.5 mm ² - rigid Screw clamp terminal (bottom) 2 cable(s) 1.5 mm ² - flexible with ferrule
Wire stripping length	9 Mm
Tightening torque	1 N.M

Environment

IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.9 Cm
Package 1 Width	2.1 Cm
Package 1 Length	9.4 Cm
Package 1 Weight	37 G
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.7 Cm
Package 2 Width	10 Cm
Package 2 Length	26.5 Cm
Package 2 Weight	501 G
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Height	30 Cm
Package 3 Width	30 Cm
Package 3 Length	40 Cm
Package 3 Weight	5.088 Kg

Offer Sustainability

SCIP Number	28bf466-f950-4025-8655-16cfe4e6c6f3
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commercialisation**

A9N26924 may be replaced by any of the following products:



A9N26904

Auxiliary contact, Acti9 A9N, OF, 1 C/O, 100mA to 6A, 24VAC to 415VAC, 24VDC to 130VDC, bottom connection

Qty 1

Substitution date: |



A9N26914

Auxiliary contact, Acti9 A9N, OF, 1 C/O, 2mA to 100mA, 24VAC to 250VAC, 24VDC to 220VDC, bottom connection

Qty 1

Substitution date: |