

AR112SH4

APC NetShelter 12U Wallmount Rack Enclosure Cabinet Single Hinged Switch Depth



Visão geral

Apresentação	Ideal for retail, healthcare, and educational facilities, this wall mount rack offers an efficient solution for deploying server and networking equipment for edge computing applications. This rack enclosure is wall mountable, ideal for areas with limited floor space, and is designed specifically for servers and network switches, and patch panels. The cabinet's door is reversible and is compatible with APC's Netbotx security upgrade to provide remote access, video surveillance, and environmental monitoring (sold separately). Optional 120V fan tray can be top or bottom mounted (sold separately) Both the top and bottom feature knockouts of 1/2U mounting space for accessories. And several APC Smart-UPS models low-profile provide easy UPS integration and mounting 12U Wall mount cabinet, mounting depth range of 2.87 to 12.95 inches, 200lb weight capacity, 19" rack width, ships fully assembled, ventilated with accessory integration options, 5 year APC warranty.
--------------	--

Prazo de entrega	Normalmente em stock
------------------	----------------------

Principal

Tipo de produto ou componente	Rack enclosure
Número de unidade de bastidor	12U

Físico

Altura	62 Cm
Largura	60 Cm
Profundidade	40 Cm
Peso líquido	14,88 Kg
Cor	Preto
Suporte de montagem	Parede
Mounting preference	No preference
Modo de montagem	Not rack-mountable
Profundidade de montagem máxima	32,89 Cm
Minimum mounting depth	7,29 Cm
Rack width	19"
Carga admissível permanente	90,7 Kg estático

Conformidade

Normas	UL 2416 EIA-310E
--------	---------------------

Unidades de Embalagem

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	70 Cm
Package 1 Width	48,5 Cm
Package 1 Length	68,5 Cm
Package 1 Weight	18,01 Kg

Sustentabilidade da oferta

Situação da oferta sustentável	Produto Green Premium
Regulamento REACh	Declaração REACh
REACh sem SVHC	Sim
Diretiva RoHS da UE	Conformidade proativa (Produto fora do âmbito RoHS da UE) Declaração-RoHS da EU
Regulamento RoHS China	Declaração RoHS China
Informações das isenções RoHS	Sim
Divulgação Ambiental	Perfil Ambiental Do Produto
Perfil de Circularidade	Informação Sobre O Fim Da Vida Útil
Eficiência energética otimizada	Produto eficiente em termos energéticos
Take-back	Take-back program available

Garantia contratual

Garantia	Reparar ou substituir 5 anos
----------	------------------------------

Product Life Status : **Comercializado**