

AR3105

Armário NetShelter SX 45U com 600 mm de
Largura x 1070 mm de Profundidade com
Lados em Preto



Visão geral

Prazo de entrega	Normalmente em stock
------------------	----------------------

Principal

Tipo de produto ou componente	Rack enclosure
Número de unidade de bastidor	45U
Equipamento fornecido	Peças de ligação Tecla(S) Portas e painéis laterais com chaves idênticas Pés de nivelamento Hardware de montagem Rodas pré-instaladas Painéis laterais

Físico

Altura	212,4 Cm
Largura	60 Cm
Profundidade	107 Cm
Peso líquido	137 Kg
Cor	Preto
Mounting preference	No preference
Modo de montagem	Not rack-mountable
Profundidade de montagem máxima	91,49 Cm
Minimum mounting depth	19,05 Cm
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge porta da frente 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Carga admissível permanente	1020,6 Kg dinâmico 1701,0 Kg estático

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Conformidade

Normas	UL 2416 UL 60950-1 EIA-310E
--------	-----------------------------------

Unidades de Embalagem

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	224 Cm
Package 1 Width	115,6 Cm
Package 1 Length	74,6 Cm
Package 1 Weight	153,7 Kg

Sustentabilidade da oferta

Situação da oferta sustentável	Produto Green Premium
Regulamento REACH	Declarção REACH
REACH sem SVHC	Sim
Diretiva RoHS da UE	Conformidade proativa (Produto fora do âmbito RoHS da UE) Declarção-RoHS da EU
Regulamento RoHS China	Declarção RoHS China
Informações das isenções RoHS	Sim
Divulgação Ambiental	Perfil Ambiental Do Produto
Perfil de Circularidade	Informação Sobre O Fim Da Vida Útil
Take-back	Take-back program available

Garantia contratual

Garantia	Reparar ou substituir 5 anos
----------	------------------------------

Product Life Status : **Comercializado**