

AR3106SP

Armário em Bastidor de Servidor NetShelter SX 18U da APC 600mm x 1070mm c/ Lados em Preto, Embalagem contra Choques



by Schneider Electric



Price*: 1646.20 EUR



Visão geral

Apresentação	An industry-standard rack with the most standard features for speed of deployment and installation. Ready for low to medium density edge computing. Shorter height allows for deployment underneath cabinets, desks, in remote office-branch office spaces for a secure and discrete solution for IT devices. Shock pallet and shock packaging simplify IT "rack and stack" for equipment integrators.
Prazo de entrega	Normalmente em stock

Geral

Equipamento fornecido	Rodízios Portas Tecla(S) Pés de nivelamento Rampas de palete Embalagem reutilizável Tecto Painéis laterais
-----------------------	---

Físico

Profundidade de montagem máxima	92,08 Cm
Número de unidade de bastidor	18U
Minimum mounting depth	19,1 Cm
Marking	14 gauge EIA mounting rail 16 gauge porta da frente 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Cor	Preto
Profundidade	107 Cm
Rack width	19"
Altura	92,5 Cm
Peso net	72,12 Kg
Carga admissível permanente	408,23 Kg dinâmico 408,23 Kg estático
Largura	60 Cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Conformidades

Normas	UL 2416 UL 60950-1 EIA-310E
--------	-----------------------------------

Unidades de embalagem

Peso da embalagem (Lbs)	127 Kg
Pacote 1 Altura	122 Cm
Pacote 1 largura	75 Cm
Pacote 1 Comprimento	124 Cm
Número de unidades no pacote 3	1

Sustentabilidade da oferta

Situação da oferta sustentável	Produto Green Premium
Regulamento REACH	Declaração REACH
REACH sem SVHC	Sim
Diretiva RoHS da UE	Conformidade proativa (Produto fora do âmbito RoHS da UE) Declaração-RoHS da EU
Eficiência energética otimizada	Produto eficiente em termos energéticos
Take-back	Take-back program available

Garantia contractual

Garantia	Reparar ou substituir 5 anos
----------	------------------------------

Product Life Status : **Comercializado**