

AR3155

Armário NetShelter SX 45U com 750 mm de Largura x 1070 mm de Profundidade com Lados em Preto



by Schneider Electric

Price*: 2837.02 EUR



Visão geral

Apresentação	This enclosure is designed to meet current IT market trends and applications ranging from high density computing and networking to broadcast and audio-video. The rack height is 45U, 750mm Wide x 1070mm Deep . It provides a reliable-rack-mounting environment for mission-critical equipment.
Prazo de entrega	Normalmente em stock

Geral

Equipamento fornecido	Peças de ligação Tecla(S) Portas e painéis laterais com chaves idênticas Pés de nivelamento Hardware de montagem Rodas pré-instaladas Painéis laterais
-----------------------	--

Físico

Profundidade de montagem máxima	91,49 Cm
Número de unidade de bastidor	45U
Minimum mounting depth	26,19 Cm
Marking	14 gauge EIA mounting rail 16 gauge porta da frente 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Cor	Preto
Profundidade	107 Cm
Rack width	19"
Altura	212,4 Cm
Peso net	155 Kg
Carga admissível permanente	1020,58 Kg dinâmico 1700,97 Kg estático
Largura	75 Cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Conformidades

Normas	UL 2416 UL 60950-1 EIA-310E
--------	-----------------------------------

Unidades de embalagem

Peso da embalagem (Lbs)	172,3 Kg
Pacote 1 Altura	224 Cm
Pacote 1 largura	85 Cm
Pacote 1 Comprimento	132 Cm
Número de unidades no pacote 3	1

Sustentabilidade da oferta

Situação da oferta sustentável	Produto Green Premium
Regulamento REACH	Declaração REACH
REACH sem SVHC	Sim
Diretiva RoHS da UE	Conformidade proativa (Produto fora do âmbito RoHS da UE) Declaração-RoHS da EU
Sem metais pesados tóxicos	Sim
Sem mercúrio	Sim
Informações das isenções RoHS	Sim
Take-back	Take-back program available

Garantia contractual

Garantia	Reparar ou substituir 5 anos
----------	------------------------------

Product Life Status : **Comercializado**