

Product data sheet


Characteristics

AZ5DE010D

Cable end, Lineryg TR cable ends, twin conductor, red, 1mm², for insulated cable, medium size, 5 sets of 50

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 0.24 USD



Main

Range of Product	Lineryg
Product or Component Type	Cable end
Cable end size	Medium
Standards	DIN 46228-4
Type of Packing	Dispenser pack
Quantity per Set	5 sets of 100
Cable cross section	0.002 In ² (1 mm ²)

Complementary

Cable end type	Twin conductor
Additional information	Without marker tag holder
Color	Red
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	2
AWG Gauge	18 AWG
Bezel size	Ø 3.4 x 5.4 mm
Tube diameter	0.09 In (2.25 mm)
Length	0.6 In (15 mm)
Tube length	0.3 In (8 mm)
Product Weight	0.31 Lb(US) (0.14 kg)

Environment

Product Certifications	cCSAus
Ambient Air Temperature for Operation	-4...221 °F (-20...105 °C)

Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110515831
Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.157 In (0.400 cm)
Package 1 Width	0.157 In (0.400 cm)
Package 1 Length	0.551 In (1.400 cm)
Package weight(Lbs)	0.004 Oz (0.100 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	500
Package 2 Height	5.157 In (13.100 cm)
Package 2 Width	2.795 In (7.100 cm)
Package 2 Length	4.961 In (12.600 cm)
Package 2 Weight	4.832 Oz (137.000 g)
Unit Type of Package 3	S02
Number of Units in Package 3	5000
Package 3 Height	5.906 In (15.000 cm)
Package 3 Width	11.811 In (30.000 cm)
Package 3 Length	15.748 In (40.000 cm)
Package 3 Weight	3.750 Lb(US) (1.701 kg)

Environmental data

REACH free of SVHC	Yes
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	No
Environmental Disclosure	Product Environmental Profile
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No, we have minimized the use of plastic in the packaging in compliance with regulations and consider
REACH Regulation	Free of Substances of Very High Concern above the threshold ↗
EU RoHS Directive	Compliant ↗
Halogen content performance	Halogen free plastic parts product
PVC free	Yes
Silicon free	Yes
Circularity Profile	End Of Life Information
Take-back	No

Contractual warranty

Warranty (in months)	18
----------------------	----

Product Life Status : **Commercialised**