

AR4024SPX429

Sala de Servidores com Isolamento Acústico Seguro NetShelter CX 24U num Armário de Caixa - Embalagem contra Choques - Preto



Visão geral

Apresentação	NetShelter CX Enclosure with integrated cooling and noise dampening is ideal for office environments. The cabinet is paired with a shock absorbing pallet, unloading ramp and impact resistant shell. The system has been engineered, tested and approved for secure shipment of fully converged systems such as being certified with Cisco® for pre-racking and shipping Cisco Unified Computing System (UCS).
Prazo de entrega	Envio habitual em 8 semanas

Geral

Equipamento fornecido	Key(S) Leveling feet Rampas de palete Embalagem reutilizável Desembalar folha
-----------------------	---

Físico

Profundidade de montagem máxima	86,21 Cm
Número de unidade de bastidor	24U
Cor	Preto
Profundidade	113 Cm
Largura do Bastidor	19"
Altura	127,5 Cm
Peso do Produto	172 Kg
Carga admissível permanente	362,87 Kg dinâmico 803,31 Kg estático
Largura	75 Cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Entrada

Frequência da rede	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	IEC 60320 C14
Tensão de entrada	100 V 110 V 115 V 120 V 127 V 200 V 208 V 220 V 230 V 240 V

Conformidades

Certificações do produto	WEEE
Normas	EIA-310D

Unidades de embalagem

Peso da embalagem (Lbs)	248 Kg
Pacote 1 Altura	155 Cm
Pacote 1 largura	100 Cm
Pacote 1 Comprimento	130 Cm
Número de unidades no pacote 3	1

Sustentabilidade da oferta

Situação da oferta sustentável	Produto Green Premium
Regulamento REACH	Declaração REACH
REACH sem SVHC	Sim
Diretiva RoHS da UE	Conformidade proativa (Produto fora do âmbito RoHS da UE) Declaração-RoHS da EU
Eficiência energética otimizada	Produto eficiente em termos energéticos

Garantia contratual

Garantia	2 anos (defeito de fabrico)
----------	-----------------------------

Product Life Status : **Comercializado**