

APC Back-UPS™ 575

Part number: BX575U-LM



Battery Backup with Automatic Voltage Regulation for Electronics and Computers

The Back-UPS 575 by APC protects your electronic equipment from damage due to power outages, surges and spikes while providing short term battery power during an outage. The Automatic Voltage Regulation feature instantly corrects voltage fluctuations without using the battery, allowing you to work indefinitely throughout voltage fluctuations and power disruptions. The Back-UPS 575 protects your PC and network connection in harsh power environments, ensuring maximum productivity and maintaining work efficiency.


Product Applications:

- PC and peripherals
- Networking equipment (router, modem)
- Network Attached Storage (NAS)
- Game console
- Projector with impulse power
- Landline cordless phone



Product Features:

- 1 Automatic Voltage Regulation (AVR)**
"Double Boost, Single Trim" AVR instantly corrects voltage fluctuations without using the battery, allowing you to work indefinitely throughout power disruptions.
- 2 Battery Backup & Surge Protected Outlets**
Keep critical electronic equipment running when the power goes out or fluctuates at dangerous levels, so you can protect your work and save your data.
- 3 3 Year Warranty**
APC offers a 3 year warranty with free technical phone and online support, assuring customer peace of mind.
- 4 Regulatory compliance**
The BX575U-LM meets the following regulatory standards: UL, FCC part15, 68, NOM.
- 5 Telephone Data Line Surge Protection**
Telephone Data Line Surge Protection defends your electronics from surges and spikes traveling over phone lines.
- 6 Push Button Circuit Breaker**
The Push-button circuit breaker provides for easy recovery from circuit overloads and protects your fuse box and electronics from electrical damage.
- 7 Building Wiring Fault Indicator**
This LED light informs you of potentially dangerous wiring problems in your wall circuit. Contact an electrician if the Wiring Fault Indicator is on.
- 8 USB Connection and PowerChute Software**
Use your computer to access additional power protection and management features:
 - Preserves your work, shuts down system during outages
 - Restarts your system, minimizing work disruptions
 - Enables customization of your Back-UPS settings
 - Monitors and displays power and battery status



APC
by Schneider Electric

Specifications

Model Number	BX575U-LM
Output	
Output Capacity	575VA / 320 Watts
Output Voltage / Frequency (On utility)	99-128Vac / 50 or 60 +/- 1Hz (Default)
Output Voltage / Frequency (On battery)	115V +/-8%, 50 or 60 Hz +/-1 Hz (auto-sensing)
Output Connections	6 NEMA Outlets (4 battery backup and surge protection and 2 surge protection only)
Waveform Type	Stepped Approximation to Sine Wave
Input	
Maximum adjustable Input Voltage / Frequency	78 - 150V / 50, 60 Hz autosensing
Input voltage range for utility operation	81 - 147 Vac (Medium Sensitivity)
Input Connection	1.5M power cable with NEMA plug
Surge Protection	
Data Line Surge Protection	Analog phone line, RJ-11 (single line, 2-wire) For phone, fax, modem, DSL
AC Power Surge Protection	All outlets
Physical	
Unit Dimensions (H x W x D)	279 x 160 x 89 mm
Unit Weight	5 Kg
Shipping Dimensions (H x W x D)	399 x 215 x 128 mm
Shipping Weight	5.2 Kg
Color	Black
UPC Code	731304310099
Battery	
Battery Type	Maintenance-free, sealed lead-acid battery, leak proof
Battery Size	12 volt, 7 Ah
Management	
Alarms	Visual (LED) and audible alarms
Adjustable Sensitivity and Transfer Voltage	Low, Medium (Default), High
USB Connectivity and Auto-Shutdown Software	PowerChute Personal Edition (Via USB interface. USB cable is included)
Warranty	3 year warranty with free technical phone and online support

APC by Schneider Electric

132 Fairgrounds Rd
West Kingston, RI 02892

www.apc.com

APC[®]
by Schneider Electric