

APC Back-UPS™ 325

Part Number: BE325-UK

Battery Backup with Surge Protection for Electronics and Computers

APC by Schneider Electric's Back-UPS 325 provides enough battery backup power so you can work through short length power outages. It also safeguards your equipment against damaging surges and spikes that travel along utility and phone lines. The Back-UPS series is "greener" than ever, using an ultra-efficient design that consumes less power during normal operation than any other battery backup in its class. This reduces your energy costs and environmental impact. Combined with all of the standard features of the Back-UPS series, the 325 is the perfect unit to protect your productivity from the constant threat of bad power and lost data.



Product Applications:

All-in-one Desktop PC
Home Networking (DSL-modem or wireless router)
CCTV
Networking Storage (NAS)
POS Equipment
Landline Cordless Phone



Product Features:

- 1 LED Indicator and Audible Alarms**
Quickly understand the unit and power status through visual and audible indicators.
- 2 4 battery backup and surge protected British sockets**
 - **2 battery backup and surge protection**
Keep critical electronic equipment running when the power goes out or fluctuates at dangerous levels, so you can protect your work and save your data.
 - **2 surge protection only**
Protect your secondary electronics from harmful surges and spikes without reducing battery capacity used to run primary electronics during power outages.
- 3 Telephone Data Line Surge Protection**
Guards against damaging surges and spikes traveling over an analog phone line.
- 4 Push Button Circuit Breaker**
Provides for easy recovery from circuit overloads and protects your fuse box and electronics from electrical damage.
- 5 Automatic Diagnostic Testing**
Periodic battery self-test ensures early detection of a battery that needs to be replaced.
- 6 2 Yr Warranty**
APC offers a 2 year warranty with free technical phone and online support, providing customer peace of mind.

Back-UPS 325 Specifications

| | |
|---|---|
| Model Number | BE325-UK |
| Output | |
| Output Capacity | 325 VA / 185 Watts |
| Output Voltage / Frequency (On utility) | 230V / 50 Hz |
| Output Voltage / Frequency (On battery) | 230V +/-8%, 47 - 63 Hz +/-1 Hz |
| Output Connections | 4 BS1363 outlets (2 battery backup and surge protection, 2 surge protection only) |
| Waveform Type | Stepped Approximation to Sine Wave |
| Input | |
| Input Voltage / Frequency | 230V / 50 Hz +/- 3 Hz |
| Input Connection | 1 x 1.8M power cord British BS1363A |
| Surge Protection | |
| AC Power Surge Protection | All outlets |
| Data Line Surge Protection | RJ-11 phone/modem/fax/DSL protection (two wire single line) |
| Physical | |
| Unit Dimensions (W x D x H) | 360 x 95 x 115 mm |
| Unit Weight | 4.00 Kg |
| Shipping Dimensions (W x D x H) | 465 x 116 x 153 mm |
| Shipping Weight | 4.60 Kg |
| Color | Black |
| UPC Code | 731304211150 |
| Battery | |
| Battery Type | Maintenance-free, sealed lead-acid battery, leak proof |
| Battery Size | 12 volt, 3 Ah |
| Management | |
| Alarms | Visual (LED) and audible alarms |
| Warranty | 2 Years Repair or Replace |

APC by Schneider Electric

132 Fairgrounds Rd
West Kingston, RI 02892

www.apc.com

APC[®]
by Schneider Electric