

## Product data sheet

### Characteristics

# DZ5CA005

Cable end, Linery TR cable ends, Single conductor, white, 0.5mm<sup>2</sup>, medium size, markable, 10 sets of 100

Product availability: Stock - Normally stocked in distribution facility

Price\*: 0.32 USD



### Main

Range of Product	Linery
Product or Component Type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of Packing	String of bags
Quantity per Set	10 sets of 100
Cable cross section	0.0008 ln <sup>2</sup> (0.5 mm <sup>2</sup> )

### Complementary

Cable end type	Single conductor
Additional information	With integrated marker tag holder
Color	White
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG Gauge	22 AWG
Bezel size	Ø 3.1 mm
Tube diameter	0.05 ln (1.3 mm)
Length	0.6 ln (14 mm)
Tube length	0.3 ln (8 mm)
CAD overall depth	1.3 ln (32 mm)
Product Weight	0.35 Lb(US) (0.16 kg)

### Environment

Product Certifications	UL
Ambient Air Temperature for Operation	-4...221 °F (-20...105 °C)

## Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110535495
Returnability	Yes
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.157 In (0.400 cm)
Package 1 Width	0.157 In (0.400 cm)
Package 1 Length	0.551 In (1.400 cm)
Package weight(Lbs)	0.004 Oz (0.100 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	1000
Package 2 Height	1.575 In (4.000 cm)
Package 2 Width	5.906 In (15.000 cm)
Package 2 Length	9.055 In (23.000 cm)
Package 2 Weight	5.150 Oz (146.000 g)
Unit Type of Package 3	S04
Number of Units in Package 3	80000
Package 3 Height	11.811 In (30.000 cm)
Package 3 Width	15.748 In (40.000 cm)
Package 3 Length	23.622 In (60.000 cm)
Package 3 Weight	27.514 Lb(US) (12.480 kg)

## Environmental data

RECh free of SVHC	Yes
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	No
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No, we have minimized the use of plastic in the packaging in compliance with regulations and considered
RECh Regulation	Free of Substances of Very High Concern above the threshold <a href="#"></a>
EU RoHS Directive	Compliant <a href="#"></a>
Halogen content performance	Halogen free plastic parts product
PVC free	Yes
Silicon free	Yes
Circularity Profile	<a href="#">End Of Life Information</a>
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and new

## Contractual warranty

Warranty (in months)	18
----------------------	----

Product Life Status : **Commercialised**