

Product data sheet

Characteristics

DZ5CE062

Cable ends, Linery TR cable ends, single conductor, green, 6mm², medium size, 10 sets of 100

Product availability: Stock - Normally stocked in distribution facility

Price*: 0.48 USD



Main

Range of Product	Linery
Product or Component Type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of Packing	Individual bag
Quantity per Set	Set of 100
Cable cross section	0.009 In ² (6 mm ²)

Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Color	Green
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG Gauge	10 AWG
Bezel size	Ø 6.9 mm
Tube diameter	0.2 In (3.9 mm)
Length	0.8 In (20 mm)
Tube length	0.5 In (12 mm)
Product Weight	0.099 Lb(US) (0.045 kg)

Environment

Product Certifications	UL
Ambient Air Temperature for Operation	-4...221 °F (-20...105 °C)

Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110537130
Returnability	Yes
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.157 In (0.400 cm)
Package 1 Width	0.157 In (0.400 cm)
Package 1 Length	0.551 In (1.400 cm)
Package weight(Lbs)	0.011 Oz (0.300 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Height	0.394 In (1.000 cm)
Package 2 Width	3.937 In (10.000 cm)
Package 2 Length	6.299 In (16.000 cm)
Package 2 Weight	1.376 Oz (39.000 g)
Unit Type of Package 3	S02
Number of Units in Package 3	10000
Package 3 Height	5.906 In (15.000 cm)
Package 3 Width	11.811 In (30.000 cm)
Package 3 Length	15.748 In (40.000 cm)
Package 3 Weight	9.248 Lb(US) (4.195 kg)

Environmental data

REACH free of SVHC	Yes
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	No
Environmental Disclosure	Product Environmental Profile
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No, we have minimized the use of plastic in the packaging in compliance with regulations and consider
REACH Regulation	Free of Substances of Very High Concern above the threshold
EU RoHS Directive	Compliant
Halogen content performance	Halogen free plastic parts product
PVC free	Yes
Silicon free	Yes
Circularity Profile	End Of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and neve

Contractual warranty

Warranty (in months)	18
----------------------	----

Product Life Status : **Commercialised**