

Product availability: Stock - Normally stocked in distribution facility

Price\*: 34.10 USD



## Main

Range	Linergy
Product name	FT
Device short name	GV1G
Product or Component Type	Terminal block
Accessory / separate part category	Connection accessory
Poles description	3P
Range compatibility	TeSys GV2 TeSys Deca TeSys U TeSys LS1

## Complementary

[Ie] rated operational current	63 A
Mounting Location	Top
IP degree of protection	IP20 conforming to IEC 60529
[Ui] rated insulation voltage	690 V IEC 60947-1
Connections - terminals	Screw clamp terminals 1 solid AWG 4 Screw clamp terminals 1 0.00...0.02 in <sup>2</sup> (1.5...16 mm <sup>2</sup> ) flexible with cable end Screw clamp terminals 1 0.00...0.02 in <sup>2</sup> (1.5...16 mm <sup>2</sup> ) flexible without cable end Screw clamp terminals 1 0.00...0.04 in <sup>2</sup> (1.5...25 mm <sup>2</sup> ) solid Screw clamp terminals 2 0.00...0.01 in <sup>2</sup> (1.5...4 mm <sup>2</sup> ) flexible with cable end Screw clamp terminals 2 0.00...0.01 in <sup>2</sup> (1.5...6 mm <sup>2</sup> ) solid Screw clamp terminals 2 0.00...0.01 in <sup>2</sup> (1.5...4 mm <sup>2</sup> ) flexible without cable end screw clamp terminals 1 flexible AWG 4
Tightening torque	15.05 Lbf.In (1.7 N.m) screw clamp terminals 19.47 Lbf.In (2.2 N.m) connector
Net Weight	0.09 Lb(US) (0.04 kg)

## Environment

Product Certifications	CE[RETURN]UKCA
------------------------	----------------

## Ordering and shipping details

Category	US101122366
Discount Schedule	0111
GTIN	3389110212570
Returnability	Yes
Country of origin	RO

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.57 In (4 cm)
Package 1 Width	1.97 In (5 cm)
Package 1 Length	2.17 In (5.5 cm)
Package 1 Weight	1.69 Oz (48 g)
Unit Type of Package 2	S02
Number of Units in Package 2	70
Package 2 Height	5.91 In (15 cm)
Package 2 Width	11.81 In (30 cm)
Package 2 Length	15.75 In (40 cm)
Package 2 Weight	8.11 Lb(US) (3.678 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	1120
Package 3 Height	30.31 In (77 cm)
Package 3 Width	31.50 In (80 cm)
Package 3 Length	23.62 In (60 cm)
Package 3 Weight	150.31 Lb(US) (68.18 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>


## Contractual warranty

Warranty	18 months
----------	-----------

---

Sets of Busbars GV2G... with Terminal Block GV1G09

---



Product Life Status :	Commercialised
-----------------------	----------------