

## Product data sheet

### Characteristics

# DZ5CE0153

Cable ends, Lineryg TR cable ends, single conductor, black, 1.5mm<sup>2</sup>, long size, 10 sets of 100

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 0.42 USD



### Main

Range of Product	Lineryg
Product or Component Type	Cable end
Cable end size	Long
Standards	NF C 63-023
Type of Packing	String of bags
Quantity per Set	10 sets of 100
Cable cross section	0.002 In <sup>2</sup> (1.5 mm <sup>2</sup> )

### Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Color	Black
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG Gauge	16 AWG
Bezel size	Ø 4 mm
Tube diameter	0.08 In (2 mm)
Length	0.9 In (24 mm)
Tube length	0.7 In (18 mm)
Product Weight	0.474 Lb(US) (0.215 kg)

### Environment

Product Certifications	UL
Ambient Air Temperature for Operation	-4...221 °F (-20...105 °C)

## Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110537192
Returnability	No
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.157 In (0.400 cm)
Package 1 Width	0.157 In (0.400 cm)
Package 1 Length	0.551 In (1.400 cm)
Package weight(Lbs)	0.004 Oz (0.100 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	1000
Package 2 Height	0.984 In (2.500 cm)
Package 2 Width	4.331 In (11.000 cm)
Package 2 Length	7.087 In (18.000 cm)
Package 2 Weight	7.372 Oz (209.000 g)
Unit Type of Package 3	S01
Number of Units in Package 3	10000
Package 3 Height	5.906 In (15.000 cm)
Package 3 Width	5.906 In (15.000 cm)
Package 3 Length	15.748 In (40.000 cm)
Package 3 Weight	5.042 Lb(US) (2.287 kg)

## Environmental data

RECh free of SVHC	Yes
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	No
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No, we have minimized the use of plastic in the packaging in compliance with regulations and consider
RECh Regulation	Free of Substances of Very High Concern above the threshold <a href="#"></a>
EU RoHS Directive	Compliant <a href="#"></a>
Halogen content performance	Halogen free plastic parts product
PVC free	Yes
Silicon free	Yes
Circularity Profile	<a href="#">End Of Life Information</a>
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and neve

## Contractual warranty

Warranty (in months)	18
----------------------	----

Product Life Status : **Commercialised**